



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288011190 | <b>Size:</b>                  | 25x8x8 mm |
| <b>Part number:</b>    | 05056240001   | <b>Weight:</b>                | 6 g       |
| <b>Article number:</b> | 800/1 TZ      | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For slotted screws
- Ductile and tough for hard materials
- Torsion design against premature wear
- 1/4" hexagon drive (Wera connecting series 1)
- Suitable for Bosch, Fein, Holz-Her, Lecloux, Metabo

Bits for slotted screws with Torsion zone to combat premature wear. Tough viscous for universal use; 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

**Web link**

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_slotted\\_screws\\_800\\_1\\_tz.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_slotted_screws_800_1_tz.html)

Wera - 800/1 TZ  
05056240001 - 4013288011190

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Bits for Slotted Screws

## TZ-Bits

## Tough-absorbing bits



TZ-Bits are tough bits with a torsion zone. Torsion bits absorb the damaging peak torque loads in the torsion zone. This prevents premature wear and enhances the service life of the bits.



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

## Further versions in this product family:

|                    | <br>mm | <br>mm | <br>mm | <br>inch | <br>mm |
|--------------------|------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| 05056203001        | 0.5                                                                                      | 4.0                                                                                      | 25                                                                                       | 1                                                                                            | 4.0                                                                                        |
| 05056210001        | 0.6                                                                                      | 4.5                                                                                      | 25                                                                                       | 1                                                                                            | 4.5                                                                                        |
| 05056220001        | 0.8                                                                                      | 5.5                                                                                      | 25                                                                                       | 1                                                                                            | 5.5                                                                                        |
| 05056225001        | 1.0                                                                                      | 5.5                                                                                      | 25                                                                                       | 1                                                                                            | 5.5                                                                                        |
| 05056233001        | 1.2                                                                                      | 6.5                                                                                      | 25                                                                                       | 1                                                                                            | 6.2                                                                                        |
| <b>05056240001</b> | <b>1.6</b>                                                                               | <b>8.0</b>                                                                               | <b>25</b>                                                                                | <b>1</b>                                                                                     | <b>8.0</b>                                                                                 |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_slotted\\_screws\\_800\\_1\\_tz.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_slotted_screws_800_1_tz.html)

Wera - 800/1 TZ

05056240001 - 4013288011190

Wera Werkzeuge GmbH

Körzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)