


Series 7400 Kraftform ESD adjustable torque screwdrivers (0.1-3.0 Nm) with  
Rapidaptor quick-release chuck, art. no. 7440 ESD x 0.3-1.2 Nm  
ESD Series



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288106964 | <b>Size:</b>                  | 188x52x57 mm |
| <b>Part number:</b>    | 05074730001   | <b>Weight:</b>                | 180 g        |
| <b>Article number:</b> | 7400 ESD      | <b>Country of origin:</b>     | CZ           |
|                        |               | <b>Customs tariff number:</b> | 82054000     |



- Adjustable Kraftform ESD torque screwdriver with Rapidaptor quick-release chuck
- ESD-safe tool thanks to surface resistance of  $< 10^9 \Omega$
- Multi-component Kraftform Micro handle for fast and ergonomic screwdriving
- Hexagonal anti-roll feature against rolling away
- Rapidaptor quick-release chuck for bits with 1/4" hex head drive

Wera torque screwdriver. Dependable protection against electrostatic energy and associated damage. Variable torque setting option with highest precision. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

**Web link**

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_variable\\_torque\\_adjustment\\_models\\_7400\\_esd.html](https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_esd.html)

Wera - 7400 ESD  
05074730001 - 4013288106964

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Series 7400 Kraftform ESD adjustable torque screwdrivers (0.1-3.0 Nm) with Rapidaptor quick-release chuck, art. no. 7440 ESD x 0.3-1.2 Nm ESD Series**



**Adjustable Torque Screwdrivers**



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

**Wera ESD Tools**



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

**Simple setting**



Simple setting of the required torque by hand.

**Easy-to-read**



Easy-to-read scale value.

**Attachable magnifying glass**




Articles 7430, 7431 and 7432 all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.

**Measurement accuracy**




Measurement accuracy is  $\pm 6\%$  (article 1430:  $\pm 10\%$ ) in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

**Unlimited torque**



Unlimited torque for loosening seized screws.

**Versatile**



Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

**Web link**

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_variable\\_torque\\_adjustment\\_models\\_7400\\_esd.html](https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_esd.html)

Wera - 7400 ESD

05074730001 - 4013288106964

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal


Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

Series 7400 Kraftform ESD adjustable torque screwdrivers (0.1-3.0 Nm) with  
Rapidaptor quick-release chuck, art. no. 7440 ESD x 0.3-1.2 Nm  
ESD Series



Further versions in this product family:

|                           |                 |  |  |  |  |  |  |
|---------------------------|-----------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                           | art. no.        | inch                                                                              | Nm                                                                                | Nm                                                                                | mm                                                                                  | mm                                                                                  | inch                                                                                |
| 05074780001 <sup>1)</sup> | 7430 ESD        | 1/4                                                                               | 0.10-0.34                                                                         | 0.015                                                                             | 89                                                                                  | 142                                                                                 | 5 7/16                                                                              |
| 05074782001 <sup>1)</sup> | 7431 ESD        | 1/4                                                                               | 0.30-1.00                                                                         | 0.05                                                                              | 89                                                                                  | 142                                                                                 | 5 7/16                                                                              |
| 05074784001 <sup>1)</sup> | 7432 ESD        | 1/4                                                                               | 0.90-1.50                                                                         | 0.05                                                                              | 89                                                                                  | 142                                                                                 | 5 7/16                                                                              |
| <b>05074730001</b>        | <b>7440 ESD</b> | <b>1/4</b>                                                                        | <b>0.3-1.2</b>                                                                    | <b>0.05</b>                                                                       | <b>105</b>                                                                          | <b>155</b>                                                                          | <b>6</b>                                                                            |
| 05074731001               | 7441 ESD        | 1/4                                                                               | 1.2-3.0                                                                           | 0.10                                                                              | 105                                                                                 | 155                                                                                 | 6                                                                                   |

1) With attachable magnifying glass, dramatically improving visibility.

Web link

[https://products.wera.de/en/torque\\_tools\\_series\\_7400\\_kraftform\\_torque\\_screwdrivers\\_variable\\_torque\\_adjustment\\_models\\_7400\\_esd.html](https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_esd.html)

Wera - 7400 ESD  
05074730001 - 4013288106964

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)