



EAN: 4013288165695
Part number: 05073675001
Article number: Kraftform Micro 12
Universal 1

Size: 245x115x55 mm
Weight: 356 g
Country of origin: CZ
Customs tariff number: 82054000

- Kraftform Micro set in a robust pouch
- Kraftform Micro handle for fast and ergonomic working
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Holding function for TORX® screws
- Take it easy tool finder: colour coding according to profile and size

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_kraftform_micro_12_universal_1.html

Wera - Kraftform Micro 12 Universal 1
05073675001 - 4013288165695



Wera Micro screwdriver set for precision mechanical work. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Storage and transport in a robust belt pouch – so the tool is always at hand.

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_kraftform_micro_12_universal_1.html

Wera - Kraftform Micro 12 Universal 1
05073675001 - 4013288165695

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:



2050 PH Micro

05118020001¹⁾ 1 x PH 00 x 60 mm

05118022001²⁾ 1 x PH 0 x 60 mm

1) Optimised for Asian PH screws

2) Size 0 modified according to JCSIS 0 (Japanese Camera Industrial Standard)



2067 TORX® HF

05118181001 1 x TX 5 x 40 mm

05118182001 1 x TX 6 x 40 mm



2035 Micro

05118002001 1 x 0.23 x 1.5 x 40 mm

05118004001 1 x 0.30 x 1.8 x 60 mm

05118006001 1 x 0.40 x 2 x 60 mm

05118008001 1 x 0.40 x 2.5 x 80 mm

05118010001 1 x 0.50 x 3 x 80 mm



2054 Micro

05118062001 1 x 0.9 x 40 mm

05118066001 1 x 1.5 x 60 mm

05118068001 1 x 2 x 60 mm



K70

11990176 1 x 70 x 50 mm

Kraftform Micro Handle




Screwdriving jobs in electrical and precision engineering applications are often tedious and time-consuming. We learned from users what is important for them: working speeds, torque, precision – and we then focused particularly on these issues.




Multi-component screwdriver handle for ergonomic working.

The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.


Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_kraftform_micro_12_universal_1.html

Wera - Kraftform Micro 12 Universal 1
05073675001 - 4013288165695


Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid twisting.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_series_kraftform_micro_kraftform_micro_12_universal_1.html

Wera - Kraftform Micro 12 Universal 1
05073675001 - 4013288165695

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de