


## Nutsetters



|                        |               |                               |             |
|------------------------|---------------|-------------------------------|-------------|
| <b>EAN:</b>            | 4013288101020 | <b>Size:</b>                  | 50x18x18 mm |
| <b>Part number:</b>    | 05060408001   | <b>Weight:</b>                | 31 g        |
| <b>Article number:</b> | 869/4         | <b>Country of origin:</b>     | CZ          |
|                        |               | <b>Customs tariff number:</b> | 82042000    |

- Nutsetter for hexagon head screws
- 1/4" hexagon drive
- Non-magnetic design
- Metric

Metric nutsetter for hexagon head screws. Non-magnetic design. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

### Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_nutsetters\\_869\\_4.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_nutsetters_869_4.html)

Wera - 869/4  
05060408001 - 4013288101020

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## 869/4 Nutsetters, 13 x 50 mm

### Nutsetters



### Non-magnetic design



Non-magnetic nutsetters that do not attract metal filings.

### Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_nutsetters\\_869\\_4.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_nutsetters_869_4.html)

Wera - 869/4  
05060408001 - 4013288101020

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Nutsetters

Further versions in this product family:

|                    |  |  |  |  |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    | mm                                                                                | inch                                                                              | mm                                                                                  | mm                                                                                  |
| 05060400001        | 5.5                                                                               |                                                                                   | 50.0                                                                                | 11.0                                                                                |
| 05060272001        | 5.5                                                                               |                                                                                   | 65.0                                                                                | 9.5                                                                                 |
| 05060401001        | 6.0                                                                               |                                                                                   | 50.0                                                                                | 11.0                                                                                |
| 05060274001        | 6.0                                                                               |                                                                                   | 65.0                                                                                | 11.0                                                                                |
| 05060402001        | 7.0                                                                               |                                                                                   | 50.0                                                                                | 11.0                                                                                |
| 05060276001        | 7.0                                                                               |                                                                                   | 65.0                                                                                | 11.0                                                                                |
| 05060403001        | 8.0                                                                               |                                                                                   | 50.0                                                                                | 12.5                                                                                |
| 05060278001        | 8.0                                                                               |                                                                                   | 65.0                                                                                | 12.5                                                                                |
| 05060404001        | 9.0                                                                               |                                                                                   | 50.0                                                                                | 14.0                                                                                |
| 05060280001        | 9.0                                                                               |                                                                                   | 65.0                                                                                | 14.0                                                                                |
| 05060405001        | 10.0                                                                              |                                                                                   | 50.0                                                                                | 14.0                                                                                |
| 05060282001        | 10.0                                                                              |                                                                                   | 65.0                                                                                | 14.0                                                                                |
| 05060406001        | 11.0                                                                              |                                                                                   | 50.0                                                                                | 16.0                                                                                |
| 05060281001        | 11.0                                                                              |                                                                                   | 65.0                                                                                | 16.0                                                                                |
| 05060407001        | 12.0                                                                              |                                                                                   | 50.0                                                                                | 18.0                                                                                |
| 05060283001        | 12.0                                                                              |                                                                                   | 65.0                                                                                | 17.0                                                                                |
| <b>05060408001</b> | <b>13.0</b>                                                                       |                                                                                   | <b>50.0</b>                                                                         | <b>18.0</b>                                                                         |
| 05060284001        | 13.0                                                                              |                                                                                   | 65.0                                                                                | 19.0                                                                                |
| 05060409001        |                                                                                   | 1/4"                                                                              | 50.0                                                                                | 11.0                                                                                |
| 05060286001        |                                                                                   | 1/4"                                                                              | 65.0                                                                                | 11.0                                                                                |
| 05060410001        |                                                                                   | 5/16"                                                                             | 50.0                                                                                | 12.5                                                                                |
| 05060290001        |                                                                                   | 5/16"                                                                             | 65.0                                                                                | 12.5                                                                                |
| 05060411001        |                                                                                   | 3/8"                                                                              | 50.0                                                                                | 14.0                                                                                |
| 05060288001        |                                                                                   | 3/8"                                                                              | 65.0                                                                                | 14.0                                                                                |
| 05060412001        |                                                                                   | 7/16"                                                                             | 50.0                                                                                | 16.0                                                                                |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_nutsetters\\_869\\_4.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_nutsetters_869_4.html)

Wera - 869/4

05060408001 - 4013288101020

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)