

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0936040071](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** GWconnect Enclosure, Die-cast Aluminum, S-8000 Series, with External Mounting Flanges, 252 x 215 x 91mm Outside Dimensions, Grey RAL 7037



**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

| General                       |                                                                                                |
|-------------------------------|------------------------------------------------------------------------------------------------|
| Product Family                | Industrial Connectors / Enclosures                                                             |
| Series                        | <a href="#">93604</a>                                                                          |
| IP Rating                     | IP66                                                                                           |
| Overview                      | <a href="#">GWconnect Heavy Duty Connectors (HDC)</a>                                          |
| Product Category              | Die-cast Enclosures                                                                            |
| Product Name                  | GWconnect                                                                                      |
| Standard                      | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 60670-1, EN 62208, EN-60670-22, NMX-J235/1-2 |
| Type                          | ATEX                                                                                           |
| UPC                           | 887191871462                                                                                   |
| Physical                      |                                                                                                |
| Enclosure Coating             | Polyester Powder                                                                               |
| Enclosure Color               | Grey RAL 7037                                                                                  |
| Internal Dimensions           | 239 x 202 x 85mm                                                                               |
| Material - Enclosure          | Die-cast Aluminum                                                                              |
| Mounting Style                | External Flanges                                                                               |
| Net Weight                    | 1390.000/g                                                                                     |
| Outside Dimensions            | 252 x 215 x 91mm                                                                               |
| Packaging Type                | Carton                                                                                         |
| Temperature Range - Operating | -20° to +85°C                                                                                  |
| Material Info                 |                                                                                                |
| Engineering Number            | 8000.6295.0                                                                                    |

|                                                                                                                                                                                                                                                   |                                              |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                                                                                                                              |                                              |
| <b>EU RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br>Not Contained Per -<br>D(2020)4578-DC (25<br>June 2020)<br><b>Halogen-Free</b><br><b>Status</b><br><b>Low-Halogen</b><br>For more information, please visit <a href="#">Contact US</a> | <b>China RoHS</b>                            |
| China ROHS<br>ELV<br>RoHS Phthalates                                                                                                                                                                                                              | Green Image<br>Not Relevant<br>Not Contained |

**Search Parts in this Series**  
[93604](#) Series

**Use With**  
DIN-rails, mounting supports, fixing screws,  
metal plates, and ground terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION