

Product information

00 21 19 LB E

KNIPEX L-BOXX® Electric

63 parts



Ideal storage and transport solution: the KNIPEX L-BOXX® with a large range of tools for professional electricians

- Strong box made of impact- and shock-proof ABS plastic
- Equipped with 14 KNIPEX tools, a total of 63 brand tools, partly VDE-tested according to DIN EN 60900
- Max. payload: 25 kg
- Splash-proof
- Several boxes can be securely joined together
- Flexible inner partitions
- Handle can be lowered into a hollow in the lid to save space
- Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- With two-piece tool board made from dirt-repellent PP twin-wall sheets
- Tool boards are connected to each other using hook-and-loop
- Top section with 10 pockets and 10 elastic straps
- Upper part of bottom section with 7 pockets and strap for hanging up the tool board; can also be used to lift or lay the KNIPEX L-BOXX® down
- Bottom of base part with 7 pockets and 7 elastic straps
- External dimensions (W x H x D): 442 x 357 x 151 mm; internal dimensions (W x H x D): 375 x 107 x 311 mm
- Strong box made of impact- and shock-proof ABS plastic

General

Article No.	00 21 19 LB E
EAN	4003773081623
weight	7,850 g
Dimensions	235 x 365 mm

Technische Attribute

Dimension exterior (interior) width mm	442 mm 375 mm
Dimension exterior (interior) height mm	151 mm 107 mm
Dimension exterior (interior) depth mm	442 mm 311 mm

Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076
UNSPSC 13.1	27112117

Content

00 11 01	KNIPEX TwinKey® for all standard cabinets and shut-off systems
08 26 145	Needle-Nose Combination Pliers
12 42 195	KNIPEX MultiStrip 10 Automatic Insulation Stripper
13 86 200	Pliers for Electrical Installation
16 95 01 SB	KNIPEX ErgoStrip® Universal Stripping Tool
26 26 200	Snipe Nose Side Cutting Pliers (Stork Beak Pliers)
70 06 160	Diagonal Cutter
74 06 200	High Leverage Diagonal Cutter

Content	
86 03 180	Pliers Wrench Pliers and a wrench in a single tool
86 03 180	Pliers Wrench Pliers and a wrench in a single tool
87 01 180	KNIPEX Cobra® Hightech Water Pump Pliers
97 53 04	Self-Adjusting Crimping Pliers for wire ferrules with lateral access
98 20 35 SL	Screwdriver (Slim) for slotted screws
98 25 01 SL	Screwdriver (Slim) for cross-recessed screws Pozidriv®
98 52	Cable Knife
101-00	Picard Locksmith's hammer
101-0300	Picard Locksmith's hammer
361 252 1	Rennsteig Electrician's Chisel
16135	Stabila Spirit Level Type 70 Electric
18115	Stabila Pocket Electric mini spirit level
L240 00055	Stabila Spirit Level Type 70 Electric
003760	Wera Joker open-end wrench
004018	Wera 8100 SA 8 Zyklop set of metal ratchets 28 parts
5003484001	Wera 16-part set of VDE interchangeable blades, slim
00 21 19 LB	KNIPEX L-BOXX® empty
00 21 19 LB WK	Tool board for KNIPEX L-BOXX®
00 21 19 LB LE	KNIPEX L-BOXX® empty

technical change and errors excepted

L-BOXX® is a registered trademark of Sortimo International GmbH