

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2002184300

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for CTX50 Small Grip Sealed Receptacle Terminals, 0.13mm² FLR2X CUSN Wire

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	CTX50
Tool Type	Hand Crimp Tool
UPC	193264594955
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents2002184300-000



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207129 Series

Application Tooling Description	FAQ Product #
CTX50 Receptacle Terminal, Sealed, Tin, S-Grip, D-Wind, Left Payoff, Wire Insulation Diameter 0.95-1.05mm	349052448
CTX50 Receptacle Terminal, Sealed, Tin, S-Grip, B-Wind, Right Payoff, Wire Insulation Diameter 0.95-1.05mm	349052450
CTX50 Receptacle Terminal, Sealed, Silver, S-Grip, D-Wind, Left Payoff, Wire Insulation Diameter 0.95-1.05mm	349056448
CTX50 Receptacle Terminal, Sealed, Silver, S-Grip, B-Wind, Right	349056450

Payoff, Wire
Insulation Diameter
0.95-1.05mm

This document was generated on 11/24/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION