

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638115900

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for MX150 Female Terminals, 14-16 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

Type: 4A

Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

N/A

Hand Crimp Tool

822350665926

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight

428.885/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-6381159HM, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
MX150 Female Terminal for Mat-Sealed Connectors, Gold Plating, 14 and 16 AWG, Right Reel Payoff	330012003
MX150 Female Terminal for Unsealed Connectors, Gold Plating, 14 and 16 AWG, Right Reel Payoff. Not suitable for MX150 Sealed Connectors.	330012021
MX150 Female Terminal for Mat-Sealed Connectors,	330013003

Gold Plating, 14 and
16 AWG, Left Reel
Payoff

MX150 Female 330013021

Terminal for
Unsealed
Connectors, Gold
Plating, 14 and 16
AWG, Left Reel
Payoff. Not suitable
for MX150 Sealed
Connectors.

MX150 Female 330014001

Terminal for Mat-
Sealed Connectors,
Silver Plating, 14 and
16 AWG, Right Reel
Payoff

MX150 Female 330014021

Terminal for
Unsealed
Connectors, Silver
Plating, 14 and 16
AWG, Right Reel
Payoff. Not suitable
for MX150 Sealed
Connectors.

MX150 Female 330015001

Terminal for Mat-
Sealed Connectors,
Silver Plating, 14 and
16 AWG, Left Reel
Payoff

MX150 Female 330015021

Terminal for
Unsealed
Connectors, Silver
Plating, 14 and 16
AWG, Left Reel
Payoff. Not suitable
for MX150 Sealed
Connectors.

MX150 Female 330122001

Terminal for Mat-
Sealed Connectors,
Tin Plating, 14 and
16 AWG, Right Reel
Payoff

MX150 Female 330122021

Terminal for
Unsealed
Connectors, Tin
Plating, 14 and 16
AWG, Right Reel
Payoff. Not suitable
for MX150 Sealed
Connectors.

MX150 Female 330123001

Terminal for Mat-
Sealed Connectors,
Tin Plating, 14 and
16 AWG, Left Reel
Payoff

MX150 Female 330123021

Terminal for

Unsealed
Connectors, Tin
Plating, 14 and 16
AWG, Left Reel
Payoff. Not Suitable
for MX150 Sealed
Connectors.

This document was generated on 02/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION