

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640013900

Status:

Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals

Documents:


RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822348039418
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	2582.000/g

Material Info	
Engineering Number	MCT-8200

Reference - Drawing Numbers	
Application Tooling Documents	ATS-640013900-001, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 8 (M4)	190670003
NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5)	190670006
NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6)	190670008
NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG	190670012

Wire, Stud Size 5/16" (M8) NylaKrimp Funnel	<u>190670016</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size (M5) NylaKrimp Funnel	<u>190670018</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6) NylaKrimp Funnel	<u>190670022</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 3/8" (M9) NylaKrimp Funnel	<u>190670025</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8) NylaKrimp Funnel	<u>190670031</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 7/16" (M11) NylaKrimp Funnel	<u>190670032</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/2" (M12) NylaKrimp Funnel	<u>190670033</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 3/4" (M18) NylaKrimp Funnel	<u>190670034</u>
Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/8" (M16) NylaKrimp Funnel	<u>190670045</u>
Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size (M5) NylaKrimp Funnel	<u>190670047</u>
Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size 1/4" (M6) NylaKrimp Funnel	<u>190670052</u>
Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size 3/8" (M9) NylaKrimp Funnel	<u>190670055</u>
Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size 5/16" (M8) NylaKrimp Funnel	<u>190670059</u>
Entry Ring Tongue Terminal for 6 AWG	

Wire, Stud Size	
7/16" (M11)	
NylaKrimp Funnel	<u>190670061</u>
Entry Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
1/2" (M12)	
NylaKrimp Funnel	<u>190670063</u>
Entry Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
3/8" (M9)	
NylaKrimp Funnel	<u>190670065</u>
Entry Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
7/16" (M11)	
NylaKrimp Funnel	<u>190670067</u>
Entry Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size 8	
(M4)	
NylaKrimp Funnel	<u>190670069</u>
Entry Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size 10	
(M5)	
NylaKrimp Funnel	<u>190670071</u>
Entry Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
1/4" (M6)	
NylaKrimp Funnel	<u>190670073</u>
Entry Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
5/16" (M8)	
NylaKrimp Funnel	<u>190670076</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size	
1/2" (M12)	
NylaKrimp Funnel	<u>190670077</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size	
1/4" (M6)	
NylaKrimp Funnel	<u>190670078</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size	
3/8" (M9)	
NylaKrimp Funnel	<u>190670079</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size	
5/16" (M8)	
NylaKrimp Funnel	<u>190670080</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size	
7/16" (M11)	
NylaKrimp Funnel	<u>190670081</u>
Entry Ring Tongue	
Terminal for 4 AWG	

Wire, Stud Size 10 (M5)	
NylaKrimp Funnel	<u>190670082</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size 1/4" (M6)	
NylaKrimp Funnel	<u>190670084</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size 5/16" (M8)	
NylaKrimp Funnel	<u>190670085</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size 1/2" (M12)	
NylaKrimp Funnel	<u>190670087</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size 5/8" (M16)	
NylaKrimp Funnel	<u>190670088</u>
Entry Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size 3/4" (M18)	
NylaKrimp Funnel	<u>190670090</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size 1/2" (M12)	
NylaKrimp Funnel	<u>190670092</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size 3/8" (M9)	
NylaKrimp Funnel	<u>190670093</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size 5/16" (M8)	
NylaKrimp Funnel	<u>190670094</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size 7/16" (M11)	
NylaKrimp Funnel	<u>190670095</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size 10 (M5)	
NylaKrimp Funnel	<u>190670096</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size 1/4" (M6)	
NylaKrimp Funnel	<u>190670097</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size 3/8" (M9)	
NylaKrimp Funnel	<u>190670098</u>
Entry Ring Tongue	
Terminal for 2 AWG	

Wire, Stud Size	
5/16" (M8)	
NylaKrimp Funnel	<u>190670099</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size	
3/4" (M18)	
NylaKrimp Funnel	<u>190670100</u>
Entry Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size	
5/8" (M16)	
NylaKrimp Funnel	<u>190670128</u>
Entry Ring Tongue	
Terminal for 8 AWG	
Wire, Stud Size	
7/16" (M11)	
InsulKrimp Ring	<u>190710134</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710136</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710140</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710144</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710148</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710153</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710162</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710164</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710166</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710173</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710176</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710178</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710180</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710182</u>
Tongue Terminal for	
8 AWG Wire	
InsulKrimp Ring	<u>190710188</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710190</u>
Tongue Terminal for	
6 AWG Wire	

InsulKrimp Ring	<u>190710193</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710196</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710201</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710208</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710218</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710221</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710225</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710229</u>
Tongue Terminal for	
6 AWG Wire	
InsulKrimp Ring	<u>190710231</u>
Tongue Terminal for	
4 AWG Wire	
InsulKrimp Ring	<u>190710234</u>
Tongue Terminal for	
4 AWG Wire	
InsulKrimp Ring	<u>190710237</u>
Tongue Terminal for	
4 AWG Wire	
InsulKrimp Ring	<u>190710240</u>
Tongue Terminal for	
4 AWG Wire	
InsulKrimp Ring	<u>190710243</u>
Tongue Terminal for	
4 AWG Wire	
InsulKrimp Ring	<u>190710250</u>
Tongue Terminal for	
4 AWG Wire	
InsulKrimp Ring	<u>190710253</u>
Tongue Terminal for	
4 AWG Wire	
InsulKrimp Ring	<u>190710272</u>
Tongue Terminal for	
2 AWG Wire	
InsulKrimp Ring	<u>190710273</u>
Tongue Terminal for	
2 AWG Wire	
InsulKrimp Ring	<u>190710279</u>
Tongue Terminal for	
2 AWG Wire	
InsulKrimp Ring	<u>190710281</u>
Tongue Terminal for	
2 AWG Wire	
InsulKrimp Ring	<u>190710283</u>
Tongue Terminal for	
2 AWG Wire	
InsulKrimp Ring	<u>190710285</u>
Tongue Terminal for	
2 AWG Wire	

InsulKrimp Ring	<u>190710334</u>
Tongue Terminal for	
8 AWG Wire	
Step Down Butt	<u>191540044</u>
Splice for 8-12 AWG	
Wire, Red with	
Yellow Stripe	
Step Down Butt	<u>191540047</u>
Splice for 6-8 AWG	
Wire, Blue with Red	
Stripe	
InsulKrimp Butt	<u>191540048</u>
Splice for 4 AWG	
Wire	
InsulKrimp Butt	<u>191540049</u>
Splice for 2 AWG	
Wire	
Perma-Seal Butt	<u>191640079</u>
Splice for 8 AWG	
Wire	
Perma-Seal Ring	<u>191640080</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 10 (M5)	
Perma-Seal Ring	<u>191640081</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 1/4" (M6)	
Perma-Seal Ring	<u>191640082</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 3/8" (M9)	
Perma-Seal Ring	<u>191640083</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 5/16" (M8)	
Perma-Seal Ring	<u>191640457</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 1/2" (M12)	
VersaKrimp Ring	<u>191930146</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 8 (M4)	
VersaKrimp Ring	<u>191930149</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 10 (M5)	
VersaKrimp Ring	<u>191930152</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 1/4" (M6)	
VersaKrimp Ring	<u>191930157</u>
Tongue Terminal for	
8 AWG Wire, Stud	
Size 5/16" (M8)	
VersaKrimp Ring	<u>191930159</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930163</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930167</u>
Tongue Terminal for	
8 AWG Wire	

VersaKrimp Ring	<u>191930171</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930179</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930184</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930186</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930187</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930192</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930195</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930198</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930200</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930202</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930204</u>
Tongue Terminal for	
8 AWG Wire	
VersaKrimp Ring	<u>191930209</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930212</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930216</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930219</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930226</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930229</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930230</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930233</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930234</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930238</u>
Tongue Terminal for	
6 AWG Wire	

VersaKrimp Ring	<u>191930243</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930245</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930248</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930251</u>
Tongue Terminal for	
6 AWG Wire	
VersaKrimp Ring	<u>191930254</u>
Tongue Terminal for	
4 AWG Wire	
VersaKrimp Ring	<u>191930258</u>
Tongue Terminal for	
4 AWG Wire	
VersaKrimp Ring	<u>191930261</u>
Tongue Terminal for	
4 AWG Wire	
VersaKrimp Ring	<u>191930278</u>
Tongue Terminal for	
4 AWG Wire	
VersaKrimp Ring	<u>191930283</u>
Tongue Terminal for	
4 AWG Wire	
VersaKrimp Ring	<u>191930285</u>
Tongue Terminal for	
4 AWG Wire	
VersaKrimp Ring	<u>191930293</u>
Tongue Terminal for	
4 AWG Wire	
VersaKrimp Ring	<u>191930297</u>
Tongue Terminal for	
2 AWG Wire	
VersaKrimp Ring	<u>191930298</u>
Tongue Terminal for	
2 AWG Wire	
VersaKrimp Ring	<u>191930299</u>
Tongue Terminal for	
2 AWG Wire	
VersaKrimp Ring	<u>191930320</u>
Tongue Terminal for	
2 AWG Wire	
NylaKrimp Butt	<u>192020054</u>
Splice for 8 AWG	
Wire	
NylaKrimp Butt	<u>192020055</u>
Splice for 6 AWG	
Wire	
NylaKrimp Butt	<u>192020056</u>
Splice for 4 AWG	
Wire	
VersaKrimp Parallel	<u>192050004</u>
Splice for 8 AWG	
Wire	
VersaKrimp Parallel	<u>192050006</u>
Splice for 6 AWG	
Wire	
VersaKrimp Parallel	<u>192050007</u>
Splice for 4 AWG	
Wire	

VersaKrimp Parallel Splice for 2 AWG Wire	<u>192050008</u>
VersaKrimp Butt Splice for 8 AWG Wire	<u>192150034</u>
Step Down Butt Splice for 8-12 AWG Wire	<u>192150037</u>
VersaKrimp Butt Splice for 6 AWG Wire	<u>192150040</u>
Step Down Butt Splice for 6-8 AWG Wire	<u>192150042</u>
VersaKrimp Butt Splice for 4 AWG Wire	<u>192150045</u>
VersaKrimp Butt Splice for 2 AWG Wire	<u>192150046</u>

This document was generated on 02/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION