

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640014300

Status:


Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Avikrimp Fully Pre-Insulated and Insulated Quick Disconnect Flags, 14-22 AWG



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

| General                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Family                 | Application Tooling                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Series                         | 207129                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Comments                       | Type RHT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Function                       | Crimp                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Geographic Area                | Global                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Level of Automation            | Manual                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| More Detailed Tech Information | applicationtooling@molex.com                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Overview                       | Application Tooling                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Product Name                   | N/A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Tool Type                      | Hand Crimp Tool                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| UPC                            | 822348077434                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Warranty Disclaimer            | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |
| Material Info                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Engineering Number             | RHT-AFIFG                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Reference - Drawing Numbers    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Application Tooling Documents  | ATS-640014300, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001                                                                                                                                                                                                                                                                                                     |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Not Reviewed                                                  |               |
| REACH SVHC                                                    |               |
| Not Contained Per - ED/61/2018 (27 June 2018)                 |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Relevant                                                  |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Not Relevant  |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

| Application Tooling Description                                                                            | FAQ Product # |
|------------------------------------------------------------------------------------------------------------|---------------|
| Avikrimp Quick Disconnect, for 18-22 AWG Wire, Female Flag, Tab 6.35 x 0.81mm                              | 190060001     |
| Avikrimp Quick Disconnect, for 18-22 AWG Wire, Female Flag, Tab 4.75 x 0.51mm                              | 190060005     |
| Flag Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm <sup>2</sup> ) Wire, Box, Tab 4.75 x 0.81mm | 190060008     |

Avikrimp Quick      190060011  
Disconnect, for 14-16  
AWG Wire, Female  
Flag, Tab 6.35 x  
0.81mm  
Avikrimp Quick      190060015  
Disconnect, for 14-16  
AWG Wire, Female  
Flag, Tab 4.75 x  
0.51mm  
Flag Avikrimp      190060017  
Quick Disconnect,  
Female, for 14-16  
(2.00-1.30mm<sup>2</sup>) Wire,  
Box, Tab 4.75 x  
0.81mm

This document was generated on 02/11/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**