

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638116900

Status:

Active

Overview:

Application Tooling

Description:

Hand Crimp Tool for Right-Angle Board-in Crimp Terminals



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207129

Field Repair, See Tooling Specification (PDF) Above.

Type: 2C

Crimp

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Hand Crimp Tool

822350856386

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

63811-6975

Reference - Drawing Numbers

Application Tooling Documents

ATS-6381169HM, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/30/2017 (7 July

2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
2.50mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn) Plating, 22-28 AWG, Reel	350211001
2.50mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Tin (Sn) Plating, 22-28 AWG, Reel	350211160
2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn)	350211201

Plating, 24-30 AWG,
Reel
2.00mm Pitch, 350211301
Board-in Male Crimp
Terminal, Right-
Angle, Pre-Plated,
24-30 AWG, Reel
2.00mm Pitch, 350211360
Board-in Male Crimp
Terminal, Right-
Angle, Post-Tin
Plated, 24-30 AWG,
Reel

This document was generated on 02/10/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION