

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638131700

Status:

Active

Overview:

Application Tooling

Description:


Extraction Tool for Pico-Clasp Wire-to-Board Terminals, 28-32 AWG

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207121
Comments	<p style=""margin-top: 0; marginbottom: 0">See Tooling Specification (PDF) Above <p style=""margin-top: 0; marginbottom: 0">Extraction Tool for removal of 501193 , and 501189 Series
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	822350359030
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	638131700, ATS-638131700-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207121 Series

Application Tooling Description	FAQ Product #
1.00mm Pitch, Pico-Clasp Receptacle Crimp Housing, Dual Row, Positive Lock, 20 Circuits, White	5011892010
1.00mm Pitch, Pico-Clasp Receptacle Crimp Housing, Dual Row, Positive Lock, 30 Circuits, White	5011893010
1.00mm Pitch, Pico-Clasp Receptacle Crimp Housing, Dual Row, Positive Lock, 40 Circuits, White	5011894010
1.00mm Pitch, Pico-Clasp Receptacle Crimp Housing, Dual Row, Positive Lock, 50 Circuits, White	5011895010
1.00mm Pitch, Pico-Clasp Female Crimp	5011937000

Terminal, Gold
Plating 0.10µm,
28-32 AWG, Reel
1.00mm Pitch, Pico- [5011938000](#)
Clasp Female Crimp
Terminal, Gold
Plating 0.38µm,
28-32 AWG, Reel
1.00mm Pitch, Pico- [5011939000](#)
Clasp Female Crimp
Terminal, Gold
Plating 0.76µm,
28-32 AWG, Reel
1.00mm Pitch, Pico- [5013300200](#)
Clasp Receptacle
Crimp Housing,
Single Row, Friction
Lock, 2 Circuits,
White
1.00mm Pitch, Pico- [5013300300](#)
Clasp Receptacle
Crimp Housing,
Single Row, Friction
Lock, 3 Circuits,
White
1.00mm Pitch, Pico- [5013300400](#)
Clasp Receptacle
Crimp Housing,
Single Row, Friction
Lock, 4 Circuits,
White
1.00mm Pitch, Pico- [5013300500](#)
Clasp Receptacle
Crimp Housing,
Single Row, Friction
Lock, 5 Circuits,
White
1.00mm Pitch, Pico- [5013300600](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 6 Circuits,
White
1.00mm Pitch, Pico- [5013300700](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 7 Circuits,
White
1.00mm Pitch, Pico- [5013300800](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 8 Circuits,
White
1.00mm Pitch, Pico- [5013300900](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 9 Circuits,
White
1.00mm Pitch, Pico- [5013301000](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive

Lock, 10 Circuits,
White
1.00mm Pitch, Pico- [5013301100](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 11 Circuits,
White
1.00mm Pitch, Pico- [5013301200](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 12 Circuits,
White
1.00mm Pitch, Pico- [5013301300](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 13 Circuits,
White
1.00mm Pitch, Pico- [5013301400](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 14 Circuits,
White
1.00mm Pitch, Pico- [5013301500](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 15 Circuits,
White
1.00mm Pitch, Pico- [5013340000](#)
Clasp Female Crimp
Terminal, Tin Plating,
28-32 AWG, Reel
1.00mm Pitch, Pico- [5013340100](#)
Clasp Female Crimp
Terminal, Tin Plating,
28-32 AWG, Bag
1.00mm Pitch, Pico- [5019390300](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 3 Circuits,
White
1.00mm Pitch, Pico- [5019390400](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 4 Circuits,
White
1.00mm Pitch, Pico- [5019390500](#)
Clasp Receptacle
Crimp Housing,
Single Row, Positive
Lock, 5 Circuits,
White