

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638132400

Status:

Active

Overview:

Application Tooling

Description:

Extraction Tool for 0.60mm CP Crimp Terminals for CMC Connector

Documents:

RoHS Certificate of Compliance (PDF)

|                                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| General                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Product Family                 | Application Tooling                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Series                         | 207121                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Comments                       | See Tooling Specification Above. Extraction Tool for removal of 98913 Series                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Function                       | Extraction                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Geographic Area                | Global                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Level of Automation            | Manual                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| More Detailed Tech Information | applicationtooling@molex.com                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Overview                       | Application Tooling                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Product Name                   | N/A                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Tool Type                      | Extraction Hand Tool                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| UPC                            | 800756720210                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Warranty Disclaimer            | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638132400, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Relevant                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Relevant |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

207121 Series

Use With

64322 , 98913 0.6mm (.02") CP Crimp Terminal for CMC connector

| Application Tooling Description                                                                          | FAQ Product # |
|----------------------------------------------------------------------------------------------------------|---------------|
| 0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.35mm <sup>2</sup> | 643221019     |
| 0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.75mm <sup>2</sup> | 643221029     |
| 0.635mm CMC CP Female Terminal, Tin Plated, for Square 0.6mm x 0.6mm Pins, Wire Size 0.5mm <sup>2</sup>  | 643221039     |

|                          |                                  |
|--------------------------|----------------------------------|
| 0.635mm CMC CP           | <a href="#"><u>643221219</u></a> |
| Female Terminal,         |                                  |
| Tin Plated, Selective    |                                  |
| 1.27µm Gold in           |                                  |
| Contact Area, for        |                                  |
| Square 0.6mm x           |                                  |
| 0.6mm Pins, Wire         |                                  |
| Size 0.75mm <sup>2</sup> |                                  |
| 0.635mm CMC CP           | <a href="#"><u>643221229</u></a> |
| Female Terminal,         |                                  |
| Tin Plated, Selective    |                                  |
| 1.27µm Gold in           |                                  |
| Contact Area, for        |                                  |
| Square 0.6mm x           |                                  |
| 0.6mm Pins, Wire         |                                  |
| Size 0.35mm <sup>2</sup> |                                  |
| 0.635mm CMC CP           | <a href="#"><u>643221239</u></a> |
| Female Terminal,         |                                  |
| Tin Plated, Selective    |                                  |
| 1.27µm Gold in           |                                  |
| Contact Area, for        |                                  |
| Square 0.6mm x           |                                  |
| 0.6mm Pins, Wire         |                                  |
| Size 0.5mm <sup>2</sup>  |                                  |
| 0.635mm CMC CP           | <a href="#"><u>643221339</u></a> |
| Female Terminal,         |                                  |
| HP Version, Tin          |                                  |
| Plated, Selective        |                                  |
| 1.27µm Gold in           |                                  |
| Contact Area, for        |                                  |
| Square 0.60mm x          |                                  |
| 0.60mm Pins, Wire        |                                  |
| Size 0.75mm <sup>2</sup> |                                  |
| 0.635mm CMC CP           | <a href="#"><u>643221349</u></a> |
| Female Terminal,         |                                  |
| HP VERSION, Tin          |                                  |
| Plated, Selective        |                                  |
| 1.27µm Gold in           |                                  |
| Contact Area, for        |                                  |
| Square 0.6mm x           |                                  |
| 0.6mm Pins, Wire         |                                  |
| Size 0.35mm <sup>2</sup> |                                  |
| 0.635mm CMC CP           | <a href="#"><u>643221359</u></a> |
| Female Terminal,         |                                  |
| HP VERSION, Tin          |                                  |
| Plated, Selective        |                                  |
| 1.27µm Gold in           |                                  |
| Contact Area, for        |                                  |
| Square 0.6mm x           |                                  |
| 0.6mm Pins, Wire         |                                  |
| Size 0.5mm <sup>2</sup>  |                                  |