

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638135700

Status:

Active

Overview:

Application Tooling

Description:

Extractor Tool for CTX64 Female Crimp Terminals

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207121

Extraction

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Extraction Hand Tool

884982012738


CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-638135700



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

207121 Series

Use With

502306 CTX64, 0.64mm Female Crimp Terminals

| Application Tooling Description                                              | FAQ Product # |
|------------------------------------------------------------------------------|---------------|
| 2.00mm Pitch EdgeLock Crimp Terminal, Phosphor Bronze, Tin (Sn) Plating,Reel | 2004490001    |
| Milli-Grid Crimp Terminal, Chain, 0.38µm Select Gold, Lead free              | 873968051     |
| 2mm MGrid Crimp Term WtB Chain Unpl                                          | 873968999     |
| NSCC Rcpt Conn Sld W/ Blk 10Ckt                                              | 1.5987881101  |
| 1.50mm Pitch NSCC, Wire-to-Wire, Receptacle Housing, Gray, 10 Circuits       | 987881201     |

1.50mm Pitch NSCC,987881208  
Sealed Female  
Housing, 10 Circuits,  
Dual Row, White  
NSCC Single Part, 987891201  
Unsealed, 1.50mm,  
Male Housing, 10  
Circuits, Dual Row,  
Black  
NSCC Single 987891208  
Part, Non-Sealed,  
1.50mm, Male  
Housing, 10 Circuits,  
Dual Row, Gray

This document was generated on 01/07/2021  
**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**