

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638274900](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for Mega-Fit Crimp Terminals, mm² Wires

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207129
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mega-Fit
Tool Type	Hand Crimp Tool
UPC	889056024174
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents [ATS-6382749HM](#), [TM-638000029-001](#)



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Reviewed Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[207129](#) Series

Use With
[76823](#) , [172063](#) Mega-Fit Female Crimp Terminals

Application Tooling Description	FAQ Product #
Mega-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 14 and 16 AWG, Reel	1720630311
Mega-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 12 AWG, Reel	1720630312
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 14 and 16 AWG, Reel	1720631311
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au)	1720631312

Plating, 12 AWG, Reel	
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 14 and 16 AWG, Reel	<u>768230321</u>
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 12 AWG, Reel	<u>768230322</u>

This document was generated on 12/10/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION