

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640012600

Status:


Active

Overview:

Application Tooling

Description:

Hand Crimp Tool



Series image - Reference only

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054805268
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

RHT-5761

Reference - Drawing Numbers

Application Tooling Documents

640012600, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
Avikrimp Quick Disconnect, Male, for 18-22 (0.80-0.35mm²), Box, Tab 6.35 x 0.81mm	190010001
Avikrimp Quick Disconnect, Male, for 18-22 (0.80-0.35mm²), Box, Tab 4.75 x 0.51mm	190010003
Avikrimp Quick Disconnect, Male, for 14-16 (2.00-1.30mm²), Box, Tab 6.35 x 0.81mm	190010006
Avikrimp Quick Disconnect,	190010008

Male, for 14-16
(2.00-1.30mm²), Box,
Tab 4.75 x 0.51mm

This document was generated on 02/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION