

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640015200

Status:


Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Insulkrimp Female Fully Insulated Quick Disconnect, 24-26 AWG



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822348327393
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Material Info	
Engineering Number	RHT-2749-CC
Reference - Drawing Numbers	
Application Tooling Documents	640015200-001, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm²), Bag, Tab 4.75 x 0.51mm, Yellow	190030064
InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm²), Bag, Tab 4.75 x 0.81mm, Dark Yellow	190030068
InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm²), Bag,	190030071

Tab 6.35 x 0.81mm, Yellow InsulKrimp Quick <u>190030138</u> Disconnect, Female, Box, Tab 4.75 x 0.51mm InsulKrimp Quick <u>190030141</u> Disconnect, Female, Box, Tab 4.75 x 0.81mm
--

This document was generated on 02/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION