

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0640034200

Status:


Active

Overview:

Application Tooling

Description:

PremiumGrade Hand Crimp Tool for Flag Krimptite/Vibrakrimp Un-insulated Female Quick Disconnect Terminals, 14-22 AWG



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822348074396
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Material Info	
Engineering Number	RHT-NIFG
Reference - Drawing Numbers	
Application Tooling Documents	ATS-640034200, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

207129 Series

Use With

Loose Piece Terminals

Application Tooling Description	FAQ Product #
Flag Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 4.75 x 0.51mm	190080001
Flag Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 4.75 x 0.81mm	190080002
Flag Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 6.35 x 0.81mm	190080006

Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 4.75 x 0.51mm	<u>190080019</u>
Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190080024</u>
VibraKrimp Quick Disconnect Flag, Female, for 18-22 AWG Wire	<u>190090001</u>
VibraKrimp Quick Disconnect Flag, Female, for 18-22 AWG Wire	<u>190090003</u>
VibraKrimp Quick Disconnect Flag, Female, for 14-16 AWG Wire	<u>190090010</u>
VibraKrimp Quick Disconnect Flag, Female, for 14-16 AWG Wire	<u>190090012</u>

This document was generated on 02/11/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION