

	DATA SHEET	
Valid from: 14-06-2019	FLEXIMARK® Collar	

The collar provides the label with effective scratch protection.

Elastic and flexible shape.

Can be used together with Trasp™ Character Strips, TMB and LMB Labels.



Technical data

Material:

Operating temperature:

Colour:

Flame retardant:

Available in PVC and as halogen free

PVC: -50°C to +80°C

Halogen free: -40°C to +80°C

Transparent

UL-94 V0

Mounting:

Thread the collars on the cables.

Other product data:

ETIM Classification:

EC001288

Advantages:

Available in PVC or as Halogenfree.

Protects the marking from scratches.

Different sizes available.

Flexible combinations.

Creator: Fleximark/LR	Document: DB83252670EN FLEXIMARK CollarCollar Version: 00	Page 1 of 3
-----------------------	--	-------------

	DATA SHEET	
Valid from: 14-06-2019	FLEXIMARK® Collar	

Product data:

Halogen free

E-nummer	LAPP Article No.	Designation	Cable Ø (mm)	Length (mm)	Colour	Quantity /PU
2972255	83252670	Transparent collar HF 1.4-5/10mm	1,4-5	10	Transparent	1000
2972256	83252671	Transparent collar HF 1.4-5/15mm	1,4-5	15	Transparent	1000
2972257	83252693	Transparent collar HF 1.4-5/23mm	1,4-5	23	Transparent	500
2972258	83252672	Transparent collar HF 1.4-5/30mm	1,4-5	30	Transparent	500
2972259	83252673	Transparent collar HF 5-11/10mm	5-11	10	Transparent	500
2972260	83252674	Transparent collar HF 5-11/15mm	5-11	15	Transparent	500
2972261	83252694	Transparent collar HF 5-11/23mm	5-11	23	Transparent	200
2972262	83252675	Transparent collar HF 5-11/30mm	5-11	30	Transparent	200

PVC

E-nummer	LAPP Article No.	Designation	Cable Ø (mm)	Length (mm)	Colour	Quantity /PU
2972280	83252640	Cable strap collar 30mm	-	30	Transparent	200
2972243	83252641	Transparent collar 2-4/10 mm	2-4	10	Transparent	1000
2972244	83252642	Transparent collar 2-4/15mm	2-4	15	Transparent	1000
2972246	83252643	Transparent collar 2-4/30mm	2-4	30	Transparent	500
2972247	83252644	Transparent collar 4-7/10mm	4-7	10	Transparent	500
2972248	83252645	Transparent collar 4-7/15mm	4-7	15	Transparent	500
2972250	83252646	Transparent collar 4-7/30mm	4-7	30	Transparent	200
2972251	83252647	Transparent collar 6-10/10mm	6-10	10	Transparent	500
2972252	83252648	Transparent collar 6-10/15mm	6-10	15	Transparent	500
2972254	83252649	Transparent collar 6-10/30mm	6-10	30	Transparent	200
2972245	83252690	Transparent collar 2-4/23mm	2-4	23	Transparent	500
2972249	83252691	Transparent collar 4-7/23mm	4-7	23	Transparent	500
2972253	83252692	Transparent collar 6-10/23mm	6-10	23	Transparent	200
2941194	83290186	Transparent collar 3-4/15mm	3-4	15	Transparent	1000
2941195	83290187	Transparent collar 8-10/16mm	8-10	16	Transparent	500
2941196	83290188	Transparent collar 0,6-1,2/10mm	0,6-1,2	10	Transparent	1000
2941197	83290189	Transparent collar 0,6-1,2/15mm	0,6-1,2	15	Transparent	1000
2941158	83290190	Cable strap collar 23mm	-	23	Transparent	200

Creator: Fleximark/LR	Document: DB83252670EN FLEXIMARK CollarCollar Version: 00	Page 2 of 3
-----------------------	--	-------------

	DATA SHEET	
Valid from: 14-06-2019	FLEXIMARK® Collar	

Related products


FLEXIMARK® offers a various range of labels and marking materials that fits in the FLEXIMARK® Collar



FLEXIMARK® LMB



FLEXIMARK® TMB



Trasp™ Character Strips

Note:
Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83252670EN FLEXIMARK CollarCollar Version: 00	Page 3 of 3
-----------------------	--	-------------