


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2004711004](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit Sigma Plug Housing, 4.20mm Pitch, Single Row, UL 94V-0, Glow-Wire Capable, 4 Circuits



Series image - Reference only

Documents:

- | | |
|---|---|
| Drawing (PDF) | Packaging Specification 2004710001-PK-000 (PDF) |
| Product Specification 2029880002-PS-000 (PDF) | Test Summary 2131370002-TS-000 (PDF) |
| Product Specification 2131370000-PS-000 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification 2131370000-AS-000 (PDF) | |

General

Product Family	Crimp Housings
Series	200471
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma
UPC	193264446421

Physical

Circuits (maximum)	4
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.740/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	2131370000-AS-000
Packaging Specification	2004710001-PK-000
Product Specification	2029880002-PS-000, 2131370000-PS-000
Sales Drawing	2004710001-SD-000
Test Summary	2131370002-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[200471](#) Series

Mates With

Mini-Fit Sigma Receptacle Housing
[2004531004](#)

Use With

Mini-Fit TPA2/Sigma Male Terminal
[172765](#) , [203070](#) . Mini-Fit Sigma Retainer
[1727092004](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION