

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0334724001

Status:


Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Mat-Sealed Female Connector Assembly, Dual Row, 4 Circuits, Keying Option A, without Connector Position Assurance, with Open Standard Grommet Cap, Black



Series image - Reference only

Documents:	
3D Model (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
3D Model	Application Specification AS-33611-001-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification PS-33472-000-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33472-100-001 (PDF)	

General	
Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
Taxonomy	Connector Housings
UPC	889056506366
Physical	
Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	8.180/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33611-001-001
Product Specification	PS-33472-000-001
Sales Drawing	334720402-001, SD-33472-0001-001

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
33472 Series

Mates With
MX150 Male Sealed Connector [33482](#)

Use With
MX150 Female Terminal [33012](#) , [33001](#)

MX150 Sealed Cavity Plug [343450001](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION