

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0334724802](#)  
**Status:** **Active**  
**Overview:** [MX150 Connector System](#)  
**Description:** MX150 Mat-Sealed Female Connector Assembly, Dual Row, 8 Circuits, Keying Option B, without Connector Position Assurance, Light Gray



Series image - Reference only

**Documents:**

- |                                                                  |                                                                     |
|------------------------------------------------------------------|---------------------------------------------------------------------|
| <a href="#">3D Model (PDF)</a>                                   | <a href="#">Application Specification AS-33472-100-CH-001 (PDF)</a> |
| <a href="#">3D Model</a>                                         | <a href="#">Application Specification AS-33611-001-001 (PDF)</a>    |
| <a href="#">Drawing (PDF)</a>                                    | <a href="#">Datasheet (PDF)</a>                                     |
| <a href="#">Product Specification PS-33472-000-001 (PDF)</a>     | <a href="#">RoHS Certificate of Compliance (PDF)</a>                |
| <a href="#">Application Specification AS-33472-100-001 (PDF)</a> |                                                                     |

**General**

|                |                                        |
|----------------|----------------------------------------|
| Product Family | Crimp Housings                         |
| Series         | <a href="#">33472</a>                  |
| Application    | Power, Wire-to-Board, Wire-to-Wire     |
| Comments       | No Connector Position Assurance (CPA)  |
| Overview       | <a href="#">MX150 Connector System</a> |
| Product Name   | MX150                                  |
| Taxonomy       | Connector Housings                     |
| UPC            | 889056886260                           |

**Physical**

|                               |                            |
|-------------------------------|----------------------------|
| Circuits (maximum)            | 8                          |
| Color - Resin                 | Gray (Light)               |
| Gender                        | Receptacle                 |
| Glow-Wire Capable             | No                         |
| Keying to Mating Part         | Yes                        |
| Lock to Mating Part           | Yes                        |
| Material - Resin              | Modified Polystyrene Alloy |
| Net Weight                    | 11.408/g                   |
| Number of Rows                | 2                          |
| Packaging Type                | Partitioned Carton         |
| Panel Mount                   | No                         |
| Pitch - Mating Interface      | 3.50mm                     |
| Polarized to Mating Part      | Yes                        |
| Stackable                     | No                         |
| Temperature Range - Operating | -40° to +125°C             |

**Material Info**

**Reference - Drawing Numbers**

|                           |                                                         |
|---------------------------|---------------------------------------------------------|
| Application Specification | AS-33472-100-001, AS-33472-100-CH-001, AS-33611-001-001 |
| Product Specification     | PS-33472-000-001                                        |
| Sales Drawing             | 334720802-001, PK-31300-903-001                         |

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Compliant     |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[33472 Series](#)

**Mates With**

MX150 Male Sealed Connector [33482](#) .  
MX150 Male Bulkhead Twist-Lock Sealed  
Connector [348404420](#) . MX150 Right-Angle  
Header [348300802](#)

**Use With**

MX150 Female Terminal [33012](#) , [33001](#)  
<br>MX150 Sealed Cavity Plug [343450001](#)  
<br>MX150 Backshell [349510811](#) ,  
[349500821](#)