



4513-SET-19 HSS-G Drill Bit Set for Metal - 19 Pcs



PRODUCT DETAILS

- Includes 19 drills from 1 mm to 10 mm x 0.5 mm in a plastic case
 - 4411 HSS-G drill bits 1 mm, 1.5 mm, 2 mm, 2.5 mm, 3 mm, 3.5 mm, 4 mm, 4.5 mm, 5 mm
 - 5.5 mm, 6 mm, 6.5 mm, 7 mm, 7.5 mm, 8 mm, 8.5 mm, 9 mm, 9.5 mm, 10 mm
 - Top angle of 130° with self-centring split-point tip for quick cutting and perfect centring
 - Drill bits have a cylindrical shank (shank equal to drill bit diameter) and designed for use in drill stands and drill drivers
 - High-speed steel (HSS) drill for drilling in bronze, brass, carbon steel, cast iron, alloy steel and stainless steel
 - Manufactured to DIN 338 N
- Includes 19 drills from 1 mm to 10 mm x 0.5 mm in a plastic case
 - High-speed steel (HSS) with ground flutes
 - Long lasting performance
 - Top angle 130°
 - Split-Point
 - Ground flutes enable fast drilling and high precision
 - DIN 338N

PRODUCT ATTRIBUTES

Product		
4513-SET-19	19	600 g

Follow the Fish!



SET CONTENT



**HSS-G Drill Bit for Metal 1 mm x 34
mm**
4413-1.00



**HSS-G Drill Bit for Metal 1.5 mm x 40
mm**
4413-1.50



**HSS-G Drill Bit for Metal 10 mm x 133
mm**
4413-10.00



**HSS-G Drill Bit for Metal 2 mm x 49
mm**
4413-2.00





**HSS-G Drill Bit for Metal 2.5 mm x 57
mm**

4413-2.50



**HSS-G Drill Bit for Metal 3 mm x 61
mm**

4413-3.00



**HSS-G Drill Bit for Metal 3.5 mm x 70
mm**

4413-3.50



**HSS-G Drill Bit for Metal 4 mm x 75
mm**

4413-4.00





**HSS-G Drill Bit for Metal 4.5 mm x 80
mm**

4413-4.50



**HSS-G Drill Bit for Metal 5 mm x 86
mm**

4413-5.00



**HSS-G Drill Bit for Metal 5.5 mm x 93
mm**

4413-5.50



**HSS-G Drill Bit for Metal 6 mm x 93
mm**

4413-6.00





HSS-G Drill Bit for Metal 6.5 mm x 101 mm

4413-6.50



HSS-G Drill Bit for Metal 7 mm x 109 mm

4413-7.00



HSS-G Drill Bit for Metal 7.5 mm x 109 mm

4413-7.50



HSS-G Drill Bit for Metal 8 mm x 117 mm

4413-8.00





**HSS-G Drill Bit for Metal 8.5 mm x 117
mm**

4413-8.50



**HSS-G Drill Bit for Metal 9 mm x 125
mm**

4413-9.00



**HSS-G Drill Bit for Metal 9.5 mm x 125
mm**

4413-9.50

