

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0334824001

Status:

Active

Overview:

MX150 Connector System

Description:

MX150 Mat-Sealed Male Connector Assembly, Dual Row, 4 Circuits, Keying Option A, without Connector Position Assurance, Black



|                                                                  |                                                                     |
|------------------------------------------------------------------|---------------------------------------------------------------------|
| Documents:                                                       |                                                                     |
| <a href="#">Drawing (PDF)</a>                                    | <a href="#">Application Specification AS-33472-100-CH-001 (PDF)</a> |
| <a href="#">3D Model</a>                                         | <a href="#">Packaging Specification PK-31300-635-001 (PDF)</a>      |
| <a href="#">3D Model (PDF)</a>                                   | <a href="#">Datasheet (PDF)</a>                                     |
| <a href="#">Product Specification PS-33472-000-001 (PDF)</a>     | <a href="#">RoHS Certificate of Compliance (PDF)</a>                |
| <a href="#">Application Specification AS-33472-100-001 (PDF)</a> |                                                                     |

|                               |                                                    |
|-------------------------------|----------------------------------------------------|
| General                       |                                                    |
| Product Family                | Crimp Housings                                     |
| Series                        | 33482                                              |
| Application                   | Power, Wire-to-Wire                                |
| Overview                      | MX150 Connector System                             |
| Product Name                  | MX150                                              |
| Taxonomy                      | Connector Housings                                 |
| UPC                           | 889056506823                                       |
| Physical                      |                                                    |
| Circuits (maximum)            | 4                                                  |
| Color - Resin                 | Black                                              |
| Gender                        | Plug                                               |
| Glow-Wire Capable             | No                                                 |
| Keying to Mating Part         | Yes                                                |
| Lock to Mating Part           | Yes                                                |
| Material - Resin              | SPS/Nylon                                          |
| Net Weight                    | 8.211/g                                            |
| Number of Rows                | 2                                                  |
| Packaging Type                | Bag                                                |
| Panel Mount                   | No                                                 |
| Pitch - Mating Interface      | 3.50mm                                             |
| Polarized to Mating Part      | Yes                                                |
| Stackable                     | No                                                 |
| Temperature Range - Operating | -40° to +125°C                                     |
| Material Info                 |                                                    |
| Reference - Drawing Numbers   |                                                    |
| Application Specification     | AS-33472-100-001, AS-33472-100-CH-001              |
| Packaging Specification       | PK-31300-635-001                                   |
| Product Specification         | PS-33472-000-001                                   |
| Sales Drawing                 | 334820402-001, PK-31300-903-001, SD-33482-0001-001 |

EU ELV  
Compliant

EU RoHS  
Compliant

REACH SVHC  
Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

Halogen-Free  
Status  
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image  
Compliant

Not Contained

Search Parts in this Series

33482 Series

Mates With

Female Dual Row Sealed Connector [33472](#)

Use With

33000 MX150 Tin (Sn) Male Terminal,  
33011 Gold (Au) Male Terminal, [343450001](#)  
MX150 Sealed Blade Cavity Plug

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION