

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0334826202

Status:


Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Mat-Sealed Male Connector Assembly, Dual Row, 12 Circuits, Keying Option B, without Connector Position Assurance, Light Gray



Series image - Reference only

Documents:	
Drawing (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
3D Model	Packaging Specification PK-31300-635-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-33472-000-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33472-100-001 (PDF)	

General	
Product Family	Crimp Housings
Series	33482
Application	Power, Wire-to-Wire
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
Taxonomy	Connector Housings
UPC	889056543064
Physical	
Circuits (maximum)	12
Color - Resin	Gray (Light)
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	14.937/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-33472-100-001, AS-33472-100-CH-001
Packaging Specification	PK-31300-635-001
Product Specification	PS-33472-000-001
Sales Drawing	334821202-001, SD-33482-0001-001

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
33482 Series

Mates With
33472 Female Dual Row Sealed Connector

Use With
33000 MX150 Tin (Sn) Male Terminal,
33011 Gold (Au) Male Terminal, 343450001
MX150 Sealed Blade Cavity Plug, MX150
Backshell 349501210 , 349501220

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION