

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0791077007

Status:


Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch Milli-Grid Receptacle, Vertical, Through Hole, Dual Row, 3.00mm Tail Length, 0.38µm Gold (Au) Selective Plating, 16 Circuits, Lead-Free



Series image - Reference only

Documents:	
3D Model	Application Specification 503940001-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-70873-0180-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-79107-001 (PDF)	

General		EU ELV	
Product Family		Not Relevant	
Series		EU RoHS	
Application		Compliant	
Component Type		REACH SVHC	
Overview		Not Contained Per -	
Product Name		D(2022)4187-DC (10	
Taxonomy		June 2022)	
UPC		Halogen-Free	
Physical		Status	
Circuits (Loaded)		Low-Halogen	
Circuits (maximum)		For more information, please visit Contact US	
Color - Resin		China ROHS	
Durability (mating cycles max)		Green Image	
Glow-Wire Capable		ELV	
Lock to Mating Part		RoHS Phthalates	
Material - Metal		Not Relevant	
Material - Plating Mating		Not Contained	
Material - Plating Termination			
Material - Resin			
Net Weight			
Number of Rows			
Orientation			
PC Tail Length			
PCB Locator			
PCB Retention			
PCB Thickness - Recommended			
Packaging Type			
Pitch - Mating Interface			
Pitch - Termination Interface			
Plating min - Mating			
Plating min - Termination			
Polarized to Mating Part			
Polarized to PCB			
Surface Mount Compatible (SMC)			
Temperature Range - Operating			
Termination Interface: Style			
Electrical			
Current - Maximum per Contact			
Voltage - Maximum			
Solder Process Data			
Duration at Max. Process Temperature (seconds)			

Search Parts in this Series

79107 Series

Mates With

Milli-Grid Header [87758](#) , [87759](#) , [87760](#) , [87831](#) , [87832](#)
 Milli-Grid Low-Halogen Header [151117](#) , [151118](#) , [151119](#) , [151120](#)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

Process Temperature max. C

WAVE

001

260

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

503940001-AS-000

PK-70873-0180-001

PS-79107-001

SDA-79107-++++-001, SDA-79107-XXXX-001

This document was generated on 01/20/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION