

Industrie Bits

Industrial Bit



020
C 6,3

Industrie Bit C 6,3 Schlitz
Industrial Bit C 6,3 Slotted



					Art.-Nr.		EAN-Code
3,0 x 0,5	25 mm	C 6,3	1/4"	10	020 300 10	4	40 07157 30066 9
3,5 x 0,6	25 mm	C 6,3	1/4"	10	020 310 10	4	40 07157 30070 6
4,0 x 0,8	25 mm	C 6,3	1/4"	10	020 410 10	5	40 07157 30079 9
5,5 x 1,0	25 mm	C 6,3	1/4"	10	020 520 10	5	40 07157 30105 5
6,5 x 1,2	25 mm	C 6,3	1/4"	10	020 610 10	6	40 07157 30119 2
8,0 x 1,2	25 mm	C 6,3	1/4"	10	020 800 10	7	40 07157 30918 1

021
C 6,3

Industrie Bit C 6,3 Pozidriv
Industrial Bit C 6,3 Pozidriv



PZ				Art.-Nr.		EAN-Code
0	25 mm	C 6,3	1/4"	021 000 10	4	40 07157 24025 5
1	25 mm	C 6,3	1/4"	021 010 10	5	40 07157 30159 8
1 (VE 100)	25 mm	C 6,3	1/4"	021 010 17	500	40 07157 30925 9
2	25 mm	C 6,3	1/4"	021 020 10	5	40 07157 30169 7
2 (VE 100)	25 mm	C 6,3	1/4"	021 020 17	520	40 07157 30928 0
3	25 mm	C 6,3	1/4"	021 030 10	6	40 07157 30180 2
3 (VE 100)	25 mm	C 6,3	1/4"	021 030 17	540	40 07157 31353 9
4	32 mm	C 6,3	1/4"	021 042 10	12	40 07157 30190 1

022
C 6,3

Industrie Bit C 6,3 Phillips
Industrial Bit C 6,3 Phillips



PH				Art.-Nr.		EAN-Code
0	25 mm	C 6,3	1/4"	022 000 10	4	40 07157 30937 2
1	25 mm	C 6,3	1/4"	022 010 10	5	40 07157 30193 2
1 (VE 100)	25 mm	C 6,3	1/4"	022 010 17	470	40 07157 30940 2
2	25 mm	C 6,3	1/4"	022 020 10	5	40 07157 30205 2
2 (VE 100)	25 mm	C 6,3	1/4"	022 020 17	510	40 07157 30943 3
3	25 mm	C 6,3	1/4"	022 030 10	6	40 07157 30218 2
3 (VE 100)	25 mm	C 6,3	1/4"	022 030 17	560	40 07157 31351 5
4	32 mm	C 6,3	1/4"	022 042 10	11	40 07157 30229 8

022
C 6,3

Industrie Bit C 6,3 Phillips „Grabber“
Industrial Bit C 6,3 Phillips "Grabber"



extra slim



PH				Art.-Nr.		EAN-Code
2	25 mm	C 6,3	1/4"	022 002 10	4	40 07157 10238 6