

034 E 6,3



Industrie Bit E 6,3 Sechskant
Industrial Bit E 6,3 Hexagon



mm				Art.-Nr.		EAN-Code
2,5	50 mm	E 6,3 1/4"	10	034 255 10	11	40 07157 30325 7
3,0	50 mm	E 6,3 1/4"	10	034 305 10	11	40 07157 30327 1
4,0	50 mm	E 6,3 1/4"	10	034 405 10	12	40 07157 30329 5
5,0	50 mm	E 6,3 1/4"	10	034 505 10	12	40 07157 30331 8
6,0	50 mm	E 6,3 1/4"	10	034 605 10	13	40 07157 30333 2
8,0	50 mm	E 6,3 1/4"	10	034 805 10	17	40 07157 31878 7

035 E 6,3



Industrie Bit E 6,3 Square
Industrial Bit E 6,3 Square



SQ				Art.-Nr.		EAN-Code
1 (2,30 mm)	50 mm	E 6,3 1/4"	10	035 105 10	11	40 07157 63601 0
2 (2,80 mm)	50 mm	E 6,3 1/4"	10	035 205 10	11	40 07157 63603 4
3 (3,30 mm)	50 mm	E 6,3 1/4"	10	035 305 10	12	40 07157 63605 8

036 E 6,3



Industrie Bit E 6,3 TORX®
Industrial Bit E 6,3 TORX®



Torx®				Art.-Nr.		EAN-Code
5	50 mm	E 6,3 1/4"	10	036 055 10	7	40 07157 50973 4
6	50 mm	E 6,3 1/4"	10	036 065 10	7	40 07157 51375 5
7	50 mm	E 6,3 1/4"	10	036 075 10	7	40 07157 51377 9
8	50 mm	E 6,3 1/4"	10	036 085 10	8	40 07157 30834 4
9	50 mm	E 6,3 1/4"	10	036 095 10	8	40 07157 30835 1
10	50 mm	E 6,3 1/4"	10	036 105 10	9	40 07157 30836 8
15	50 mm	E 6,3 1/4"	10	036 155 10	8	40 07157 24026 2
20	50 mm	E 6,3 1/4"	10	036 205 10	9	40 07157 30839 9
25	50 mm	E 6,3 1/4"	10	036 255 10	9	40 07157 30841 2
27	50 mm	E 6,3 1/4"	10	036 275 10	9	40 07157 30843 6
30	50 mm	E 6,3 1/4"	10	036 305 10	11	40 07157 30845 0
40	50 mm	E 6,3 1/4"	10	036 405 10	12	40 07157 30847 4