

063

E-smart Griff

E-smart handle



Art.-Nr.



EAN-Code

063 105 00

42

40 07157 51749 4

063

E-smart VDE - Wechselklinge

E-smart VDE - Interchangeable blade



1000 V
IEC 60900:2018



Art.-Nr.



EAN-Code

Blade Size	Length	Qty	Art.-Nr.	Container	EAN-Code
2,5 x 0,4	75 mm	1	063 025 04	30	40 07157 51721 0
3,0 x 0,5	100 mm	1	063 030 04	34	40 07157 51723 4
3,5 x 0,6	100 mm	1	063 035 04	37	40 07157 51725 8
4,0 x 0,8	100 mm	1	063 040 04	37	40 07157 51727 2
5,5 x 1,0	100 mm	1	063 055 04	45	40 07157 51729 6
6,5 x 1,2	100 mm	1	063 065 04	53	40 07157 51731 9
PH 1	80 mm	1	063 102 04	48	40 07157 51733 3
PH 2	100 mm	1	063 203 04	57	40 07157 51735 7
PZ 1	80 mm	1	063 102 14	41	40 07157 51737 1
PZ 2	100 mm	1	063 203 14	57	40 07157 51739 5
Torx® 8	100 mm	1	063 083 04	35	40 07157 51741 8
Torx® 10	100 mm	1	063 103 04	37	40 07157 51743 2
Torx® 15	100 mm	1	063 153 04	37	40 07157 51745 6
Torx® 20	100 mm	1	063 203 24	41	40 07157 51747 0
H 1	80 mm	1	063 112 04	48	40 07157 51887 3
H 2	100 mm	1	063 223 04	57	40 07157 51889 7
Z 1	80 mm	1	063 112 14	41	40 07157 51891 0
Z 2	100 mm	1	063 223 14	57	40 07157 51893 4
SQ0 (1,75 mm)	100 mm	1	063 000 04	34	40 07157 53089 9
SQ1 (2,30 mm)	100 mm	1	063 100 04	37	40 07157 53091 2
SQ2 (2,80 mm)	100 mm	1	063 200 04	57	40 07157 53093 6
SQ3 (3,30 mm)	100 mm	1	063 300 04	57	40 07157 53095 0

063

Schaltschrankschlüssel Universal

Cabinet Key universal



(1 x) Spanner 10

(3 x) 5 mm, 6, 7

(1 x) 9 mm

(1 x) 3 - 5 mm

(1 x) 1/4"



Art.-Nr.



EAN-Code

063 999 01

157

40 07157 62417 8