

## 061 6,3 mm



### Industrie Umsteckbit 1/4" Pozidriv Industrial Reversible Bit 1/4" Pozidriv



| PZ  | ↔     | ⬢    | 📦  | Art.-Nr.   | 📦  | EAN-Code         |
|-----|-------|------|----|------------|----|------------------|
| 1/2 | 60 mm | 1/4" | 10 | 061 126 10 | 13 | 40 07157 30429 2 |
| 2/2 | 60 mm | 1/4" | 10 | 061 226 10 | 13 | 40 07157 50522 4 |
| 2/3 | 60 mm | 1/4" | 10 | 061 236 10 | 14 | 40 07157 30431 5 |

## 062 6,3 mm



### Industrie Umsteckbit 1/4" Phillips Industrial Reversible Bit 1/4" Phillips



| PH  | ↔     | ⬢    | 📦  | Art.-Nr.   | 📦  | EAN-Code         |
|-----|-------|------|----|------------|----|------------------|
| 1/2 | 60 mm | 1/4" | 10 | 062 126 10 | 12 | 40 07157 30433 9 |
| 2/2 | 60 mm | 1/4" | 10 | 062 226 10 | 13 | 40 07157 50524 8 |
| 2/3 | 60 mm | 1/4" | 10 | 062 236 10 | 13 | 40 07157 30435 3 |

## 063 6,3 mm



### Industrie Umsteckbit 1/4" Phillips/Schlitz Industrial Reversible Bit 1/4" Phillips/Slotted



| PH      | ↔     | ⬢    | 📦  | Art.-Nr.   | 📦  | EAN-Code         |
|---------|-------|------|----|------------|----|------------------|
| 5,5 PH2 | 60 mm | 1/4" | 10 | 063 255 10 | 12 | 40 07157 32556 3 |

## 070 C 8



### Industrie Bit C 8 Schlitz Industrial Bit C 8 Slotted



| ⬢          | ⬢     | ↔   | ⬢     | 📦  | Art.-Nr.   | 📦  | EAN-Code         |
|------------|-------|-----|-------|----|------------|----|------------------|
| 5,5 x 0,8  | 32 mm | C 8 | 5/16" | 10 | 070 514 10 | 8  | 40 07157 30988 4 |
| 5,5 x 1,0  | 32 mm | C 8 | 5/16" | 10 | 070 524 10 | 8  | 40 07157 30989 1 |
| 6,0 x 1,0  | 32 mm | C 8 | 5/16" | 10 | 070 604 10 | 9  | 40 07157 30990 7 |
| 6,5 x 1,2  | 32 mm | C 8 | 5/16" | 10 | 070 614 10 | 9  | 40 07157 30991 4 |
| 8,0 x 1,2  | 32 mm | C 8 | 5/16" | 10 | 070 804 10 | 11 | 40 07157 30992 1 |
| 8,0 x 1,6  | 32 mm | C 8 | 5/16" | 10 | 070 814 10 | 11 | 40 07157 30993 8 |
| 10,0 x 1,6 | 38 mm | C 8 | 5/16" | 10 | 070 104 10 | 17 | 40 07157 30986 0 |
| 12,0 x 2,0 | 38 mm | C 8 | 5/16" | 10 | 070 204 10 | 21 | 40 07157 30987 7 |

## 071 C 8



### Industrie Bit C 8 Pozidriv Industrial Bit C 8 Pozidriv



| PZ |  |     |  |  | Art.-Nr.   |  | EAN-Code         |
|----|-------------------------------------------------------------------------------------|-----|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------|---------------------------------------------------------------------------------------|------------------|
| 1  | 32 mm                                                                               | C 8 | 5/16"                                                                               | 10                                                                                  | 071 010 10 | 9                                                                                     | 40 07157 30994 5 |
| 2  | 32 mm                                                                               | C 8 | 5/16"                                                                               | 10                                                                                  | 071 020 10 | 10                                                                                    | 40 07157 30995 2 |
| 3  | 32 mm                                                                               | C 8 | 5/16"                                                                               | 10                                                                                  | 071 030 10 | 11                                                                                    | 40 07157 30996 9 |
| 4  | 38 mm                                                                               | C 8 | 5/16"                                                                               | 10                                                                                  | 071 042 10 | 17                                                                                    | 40 07157 30997 6 |