

900



N°9 - Schlitz-Schraubendreher mit 2K-Griff

N°9 - Slotted-Screwdriver with 2C-handle



							Art.-Nr.		EAN-Code
2,5 x 0,4 EI	75	80	28	2,5	12		900 022 10	30	40 07157 51481 3
3,0 x 0,5 EI	80	80	28	3,0	12		900 032 10	30	40 07157 51483 7
3,5 x 0,6 EI	100	80	28	3,5	12		900 353 10	35	40 07157 51485 1
4,0 x 0,8 EI	100	90	31	4,0	12		900 043 10	50	40 07157 51487 5
5,5 x 1,0	125	100	34	5,0	12		900 554 10	80	40 07157 51489 9
6,5 x 1,2	150	100	34	6,0	12		900 655 10	95	40 07157 51491 2
8,0 x 1,2	175	109	38	7,0	6		900 086 10	130	40 07157 51493 6

EI= Elektriker Klinge / EI = electrician blade

901



N°9 - Pozidriv-Schraubendreher mit 2K-Griff

N°9 - Pozidriv-Screwdriver with 2C-handle



PZ							Art.-Nr.		EAN-Code
0	60	80	28	3,0	6		901 001 10	30	40 07157 64709 2
1	80	90	31	4,5	6		901 102 10	50	40 07157 51503 2
2	100	100	34	6,0	12		901 203 10	85	40 07157 51505 6
3	150	109	38	8,0	6		901 305 10	145	40 07157 51507 0

902



N°9 - Phillips-Schraubendreher mit 2K-Griff

N°9 - Phillips-Screwdriver with 2C-handle



PH							Art.-Nr.		EAN-Code
0	60	80	28	3,0	6		902 001 10	30	40 07157 51495 0
1	80	90	31	4,5	6		902 102 10	50	40 07157 51497 4
2	100	100	34	6,0	12		902 203 10	85	40 07157 51499 8
3	150	109	38	8,0	6		902 305 10	145	40 07157 51501 8

908



N°9 - TORX®-Schraubendreher mit 2K-Griff

N°9- TORX®-Screwdriver with 2C-handle



TORX®							Art.-Nr.		EAN-Code
6	60	80	28	3,0	6		908 061 40	30	40 07157 64711 5
7	60	80	28	3,0	6		908 071 40	30	40 07157 64713 9
8	60	80	28	3,0	6		908 083 40	30	40 07157 64715 3
9	60	80	28	3,5	6		908 093 40	30	40 07157 64717 7
10	100	90	31	3,5	12		908 103 40	45	40 07157 64719 1
15	100	90	31	4,0	12		908 153 40	50	40 07157 64721 4
20	100	100	34	5,0	12		908 203 40	75	40 07157 64723 8
25	100	100	34	5,0	12		908 253 40	80	40 07157 64725 2
27	115	109	38	5,0	6		908 273 40	95	40 07157 64727 6
30	115	109	38	6,0	6		908 303 40	100	40 07157 64729 0