

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0451300401

Status:


Active

Overview:

Nano-Fit Power Connectors

Description:

Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Dual Row, 150.00mm Length, 4 Circuits, Black



Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	45130
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Overmolded	No
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	191128142113
Physical	
Cable Length	150.00mm
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	5.800/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.46mm
Wire Size AWG	20
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	8.0A
Voltage - Maximum	250V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2012341658-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

45130 Series

Mates With

Nano-Fit Vertical Through Hole Headers [1053101204](#) , [1053101304](#) , [1053101404](#) , [1053121204](#) , [1053121304](#) , [1053121404](#) . Nano-Fit Right-Angle Through Hole Headers [1053141204](#) , [1053141304](#) , [1053141404](#) . Nano-Fit Vertical SMT Headers [1054291204](#) , [1054291304](#) , [1054291404](#) . Nano-Fit Right-Angle SMT Headers [1054051204](#) , [1054051304](#) . Nano-Fit Plug Housing [2014441104](#) , [2014441204](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION