

030 E 6,3



Industrie Bit E 6,3 Schlitz

Industrial Bit E 6,3 Slotted



					Art.-Nr.		EAN-Code
3,0 x 0,5	50 mm	E 6,3	1/4"	10	030 305 10	8	40 07157 30772 9
3,5 x 0,6	50 mm	E 6,3	1/4"	10	030 315 10	8	40 07157 30275 5
4,0 x 0,8	50 mm	E 6,3	1/4"	10	030 415 10	9	40 07157 30277 9
5,5 x 1,0	50 mm	E 6,3	1/4"	10	030 525 10	10	40 07157 30285 4
6,5 x 1,2	50 mm	E 6,3	1/4"	10	030 615 10	12	40 07157 30290 8
8,0 x 1,6	50 mm	E 6,3	1/4"	10	030 815 10	14	40 07157 30294 6
10,0 x 1,6	50 mm	E 6,3	1/4"	10	030 105 10	17	40 07157 30272 4

031 E 6,3



Industrie Bit E 6,3 Pozidriv

Industrial Bit E 6,3 Pozidriv



PZ					Art.-Nr.		EAN-Code
1	50 mm	E 6,3	1/4"	10	031 015 10	9	40 07157 30309 7
2	50 mm	E 6,3	1/4"	10	031 025 10	11	40 07157 30312 7
3	50 mm	E 6,3	1/4"	10	031 035 10	11	40 07157 30315 8

032 E 6,3



Industrie Bit E 6,3 Phillips

Industrial Bit E 6,3 Phillips



PH					Art.-Nr.		EAN-Code
0	50 mm	E 6,3	1/4"	10	032 005 10	8	40 07157 51015 0
1	50 mm	E 6,3	1/4"	10	032 015 10	9	40 07157 30317 2
2	50 mm	E 6,3	1/4"	10	032 025 10	11	40 07157 30320 2
2 (VE 100)	50 mm	E 6,3	1/4"	100	032 025 17	1100	40 07157 31956 2
3	50 mm	E 6,3	1/4"	10	032 035 10	12	40 07157 30323 3

033 E 6,3



Industrie Bit E 6,3 TORX PLUS®

Industrial Bit E 6,3 TORX PLUS®



Torx Plus®					Art.-Nr.		EAN-Code
10 IP	50 mm	E 6,3	1/4"	10	033 105 10	8	40 07157 51363 2
15 IP	50 mm	E 6,3	1/4"	10	033 155 10	9	40 07157 51365 6
20 IP	50 mm	E 6,3	1/4"	10	033 205 10	9	40 07157 51367 0
25 IP	50 mm	E 6,3	1/4"	10	033 255 10	10	40 07157 51369 4
30 IP	50 mm	E 6,3	1/4"	10	033 305 10	11	40 07157 51371 7