

## 030 E 6,3



### Industrie Bit E 6,3 Schlitz

Industrial Bit E 6,3 Slotted



|                   |       |       |      |    | Art.-Nr.          |    | EAN-Code         |
|-------------------|-------|-------|------|----|-------------------|----|------------------|
| <b>3,0 x 0,5</b>  | 50 mm | E 6,3 | 1/4" | 10 | <b>030 305 10</b> | 8  | 40 07157 30772 9 |
| <b>3,5 x 0,6</b>  | 50 mm | E 6,3 | 1/4" | 10 | <b>030 315 10</b> | 8  | 40 07157 30275 5 |
| <b>4,0 x 0,8</b>  | 50 mm | E 6,3 | 1/4" | 10 | <b>030 415 10</b> | 9  | 40 07157 30277 9 |
| <b>5,5 x 1,0</b>  | 50 mm | E 6,3 | 1/4" | 10 | <b>030 525 10</b> | 10 | 40 07157 30285 4 |
| <b>6,5 x 1,2</b>  | 50 mm | E 6,3 | 1/4" | 10 | <b>030 615 10</b> | 12 | 40 07157 30290 8 |
| <b>8,0 x 1,6</b>  | 50 mm | E 6,3 | 1/4" | 10 | <b>030 815 10</b> | 14 | 40 07157 30294 6 |
| <b>10,0 x 1,6</b> | 50 mm | E 6,3 | 1/4" | 10 | <b>030 105 10</b> | 17 | 40 07157 30272 4 |

## 031 E 6,3



### Industrie Bit E 6,3 Pozidriv

Industrial Bit E 6,3 Pozidriv



| <b>PZ</b> |       |       |      | Art.-Nr.          |    | EAN-Code         |
|-----------|-------|-------|------|-------------------|----|------------------|
| <b>1</b>  | 50 mm | E 6,3 | 1/4" | <b>031 015 10</b> | 9  | 40 07157 30309 7 |
| <b>2</b>  | 50 mm | E 6,3 | 1/4" | <b>031 025 10</b> | 11 | 40 07157 30312 7 |
| <b>3</b>  | 50 mm | E 6,3 | 1/4" | <b>031 035 10</b> | 11 | 40 07157 30315 8 |

## 032 E 6,3



### Industrie Bit E 6,3 Phillips

Industrial Bit E 6,3 Phillips



| <b>PH</b>         |       |       |      | Art.-Nr.          |      | EAN-Code         |
|-------------------|-------|-------|------|-------------------|------|------------------|
| <b>0</b>          | 50 mm | E 6,3 | 1/4" | <b>032 005 10</b> | 8    | 40 07157 51015 0 |
| <b>1</b>          | 50 mm | E 6,3 | 1/4" | <b>032 015 10</b> | 9    | 40 07157 30317 2 |
| <b>2</b>          | 50 mm | E 6,3 | 1/4" | <b>032 025 10</b> | 11   | 40 07157 30320 2 |
| <b>2 (VE 100)</b> | 50 mm | E 6,3 | 1/4" | <b>032 025 17</b> | 1100 | 40 07157 31956 2 |
| <b>3</b>          | 50 mm | E 6,3 | 1/4" | <b>032 035 10</b> | 12   | 40 07157 30323 3 |

## 033 E 6,3



### Industrie Bit E 6,3 TORX PLUS®

Industrial Bit E 6,3 TORX PLUS®



| <b>Torx Plus®</b> |       |       |      | Art.-Nr.          |    | EAN-Code         |
|-------------------|-------|-------|------|-------------------|----|------------------|
| <b>10 IP</b>      | 50 mm | E 6,3 | 1/4" | <b>033 105 10</b> | 8  | 40 07157 51363 2 |
| <b>15 IP</b>      | 50 mm | E 6,3 | 1/4" | <b>033 155 10</b> | 9  | 40 07157 51365 6 |
| <b>20 IP</b>      | 50 mm | E 6,3 | 1/4" | <b>033 205 10</b> | 9  | 40 07157 51367 0 |
| <b>25 IP</b>      | 50 mm | E 6,3 | 1/4" | <b>033 255 10</b> | 10 | 40 07157 51369 4 |
| <b>30 IP</b>      | 50 mm | E 6,3 | 1/4" | <b>033 305 10</b> | 11 | 40 07157 51371 7 |