







Compliance: RohS III (2015/863/EU)

Tolerances: $\leq 10\text{mm}$: $\geq 10\text{mm}$:			Date	Name	DRR 60010	
			08/07	dr		
Material	02/21	dr			30 11 90	
Soldering conditions	01/11	dr				
IP rating	06/09	dr				
Operating temperature	09/08	dr				
Temperatures	01/08	dr			Page 1/2	
Modifications	Date	Name				

knitter-switch

Specifications:

Contact rating:	switching: 150mA, 42V DC non-switching: 200mA, 42V DC
Contact resistance:	80mOhm max.
Insulation resistance:	100MOhm min.
Mechanical life:	10 000 cycles
Operating force:	700gf max.
Operating temperature:	-40°C to +85°C
Storage temperature:	-40°C to +85°C
Soldering conditions:	pre-heat: max. 120°C, max. 70sec. wave soldering: max. 260°C, max. 10sec.
IP rating:	IP67
Material:	Cover: PA66, white O-ring: silicone, black Actuator: POM, gray PCB: epoxy Base: PA66, black Terminal / contact: phosphor bronze, min. 0.07µm gold plated over min. 0.1µm nickel

BCD

	Real coded				
	C	1	2	4	8
0	●				
1	●	●			
2	●		●		
3	●	●	●		
4	●			●	
5	●	●		●	
6	●		●	●	
7	●	●	●	●	
8	●				●
9	●	●			●

Compliance: RohS III (2015/863/EU)

Tolerances: ≤ 10mm: ≥ 10mm:			Date	Name	DRR 60010			
			08/07	dr				
Material	02/21	dr						
Soldering conditions	01/11	dr						
IP rating	06/09	dr	knitter-switch		30 11 90			Page
Operating temperature	09/08	dr						
Temperatures	01/08	dr						2/2
Modifications	Date	Name						