




CONTACT ARRANGEMENT

code for x	function	connected terminals
D	ON - ON	1-2 alternating with 2-3
F	ON - MOM	rest position: 1-2; pushed down: 2-3

RATING

y	contacts	all other conductive parts	rating DC	rating AC
empty	Ag (solid)	Brass, 10 µm Ag over 1.5 µm Ni	6V / 6 A 12V / 5 A 30 V / 4 A	125 V / 6 A 250 V / 3 A
B	Brass, 2 µm Au over 3 µm Ni	Brass, 2 µm Au over 3 µm Ni	max. 0.4 VA, max. 20 V AC/DC	
G	Ag (solid), 2 µm Au over 3 µm Ni	Brass, 2 µm Au over 3 µm Ni	6V / 6 A 12V / 5 A 30 V / 4 A 150 V / 10 mA	125 V / 6 A 250 V / 3 A


Min. rating for silver contacts: 10mA, 5V AC/DC
Min. rating for gold plated contacts: 1µA, 20mV AC/DC

Specifications:

Contact resistance: 20mOhm max.
Insulation resistance: 1 000MOhm min. at 500V DC
Dielectric strength: 1 500V, 50Hz for the duration of 1 minute
Operating temperature: -45°C to +140°C
Mechanical life: min. 30 000 cycles
Soldering conditions: hand-soldering: max.: 420°C, 3sec., 60W
auto-soldering: max.: 270°C, 5sec.
Mounting instruction: max. torque: 137Ncm
Material: Case: DAP
Housing: stainless steel, CNS9265
Bushing: copper alloy, C3604BD nickel plated
Actuator: copper alloy, C3604BD chrome plated
Included accessories: 2 pcs. nut 15/32-32, nickel plated, 14mm wrench size
1 pc. tooth washer
1 pc. locking washer

Compliance: RohS II (2011/65/EU)

PANEL MOUNTING



Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date	Name	MPG 106 x y		
			07/09	dr			
Contact arrangement	07/15	dr					
Revised	11/11	dr					
Dimension	01/11	dr	knitter-switch		30 18 88		Page
Travel	02/10	dr					1/1
Actuator dim	07/09	ok					
Modifications	Date	Name					