

Oval tubular handles

Mounting from the operator's side

SPECIFICATION

Handle tube

Aluminium

Handle shanks

Zinc die casting

plastic coated

Tube **SW**

plastic coated

black, RAL 9005, textured finish

Handle shanks

black, RAL 9005, textured finish

Tube **EL**

anodized, natural colour

Handle shanks

black, RAL 9005, textured finish

Tube **ES**

anodized, natural colour

Handle shanks

silver, RAL 9006, textured finish

Cover caps

plastic, light grey


INFORMATION

Oval tubular handles GN 334.1 are highly stable.

The handle tube can be mounted without any further machining, allowing **special lengths** to be realised easily.

TECHNICAL INFORMATION

- Load rating information (see page A35)



* Complete with Finish of the Oval tubular handles (SW, EL or ES)

SW	EL	ES
black	anodized, black	anodized, silver

GN 334.1

Description	b1	l1 ±0.5	a	b2	d	h1	h2	h3	l2	l3	l4	Δ
GN 334.1-36-200-*	36	200	24	38	8.5	57	72	5	14.5	7.5	41	430
GN 334.1-36-250-*	36	250	24	38	8.5	57	72	5	14.5	7.5	41	475
GN 334.1-36-300-*	36	300	24	38	8.5	57	72	5	14.5	7.5	41	522
GN 334.1-36-350-*	36	350	24	38	8.5	57	72	5	14.5	7.5	41	567
GN 334.1-36-400-*	36	400	24	38	8.5	57	72	5	14.5	7.5	41	613
GN 334.1-36-500-*	36	500	24	38	8.5	57	72	5	14.5	7.5	41	705
GN 334.1-36-600-*	36	600	24	38	8.5	57	72	5	14.5	7.5	41	797
GN 334.1-36-800-*	36	800	24	38	8.5	57	72	5	14.5	7.5	41	889