




ELESA Original design ERM.SST

1	2			2								
l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
44	M 4	M 5	M 6	B 5	B 6	10	14,5	24,5	3,5	30	3,5	8
63	M 6	M 8	-	B 8	-	13,5	18	31	3,5	38	4	10
78	M 8	M 10	M 12	B 8	B 10	16	21,5	36	3,5	46	4	14
95	M 10	M 12	-	B 12	-	19	25	43	5	56	4	17

Specification

3

- Handle
 - Zinc die casting
- Plastic coated
 - black, RAL 9005, textured finish
 - orange, RAL 2004, textured finish
 - red, RAL 3000, textured finish
 - silver, RAL 9006, textured finish
- Bushing and retaining screw
 - Stainless Steel AISI 303
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- RoHS

● SW

● OS

● RS

● SR

Information

3

Adjustable clamping levers GN 602.1 like all the products of the Ergostyle® family are renowned for their good style but also their ergonomic shape.

The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- Produktfamilie Ergostyle® → Page 17
- Adjustable hand levers GN 604.1 (Lever plastic, with bushing in Stainless Steel) → Page 340