


■ Features

- High Luminous LEDs
- 5mm Rocket Standard Directivity
- UV Resistant Epoxy
- Water Clear Type

■ Applications

- Automotive Dashboard Lighting
- Back Lighting
- Other Lighting

■ Outline Dimension




■ Absolute Maximum Rating

(Ta=25°C)

Item	Symbol	Value		Unit
		W/M/K/B/TG	YG/Y/O/R	
DC Forward Current	I _F	30	30	mA
Pulse Forward Current*	I _{FP}	100	100	mA
Reverse Voltage	V _R	5	5	V
Power Dissipation	P _D	102	78	mW
Operating Temperature	T _{opr}	-30 ~ +85		°C
Storage Temperature	T _{stg}	-40 ~ +100		°C
Lead Soldering Temperature	T _{sol}	260 °C/5sec		-

*Pulse width Max.10ms Duty ratio max 1/10

■ Directivity



■ Electrical -Optical Characteristics

(Ta=25°C)

Part Number	Color			V _F (V)			I _R (μA)	I _v (mcd)			λ _D (nm)			θ1/2 (deg)
				Min.	Typ.	Max.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	Typ.
				I _F =20mA			V _R =5V	I _F =20mA			I _F =20mA			
OSW5DK58A1B	White	W		-	2.9	3.4	10	1560	2180		X=0.27,Y=0.28			100
OSM5DK58A1B	Warm white	M		-	2.9	3.4	10	1120	1560		X=0.45,Y=0.41			100
OSK5DK58A1B	Pink	K5		-	2.9	3.4	10	750	1120		X=0.45,Y=0.17			100
OSB64K58A1B	Ice blue	B6		-	2.9	3.4	10	2180	3000		X=0.19,Y=0.29			100
OSB5SA58A1B	Blue	B		-	2.9	3.4	10	1120	1560		465	465	475	100
OSG5DA58A1B	True green	TG		-	2.9	3.4	10	1560	2180		520	525	530	100
OSY5PA58A1B	Yellow	Y		-	2.1	2.6	10	1120	1560		585	590	595	100
OSO5PA58A1B	Orange	O		-	2.1	2.6	10	1120	1560		600	605	610	100
OSR5PA58A1B	Red	R		-	2.1	2.6	10	1120	1560		620	625	630	100

*1 Tolerance of measurements of chromaticity coordinates is ±10%

*2 Tolerance of measurements of dominant wavelength is ±1nm

*3 Tolerance of measurements of luminous intensity is ±15%

*4 Tolerance of measurements of forward voltage is ±0.1V