


# Pozi pan head tapping screws form Z, with cone end type C

BN 13259



|               |                                                                       |
|---------------|-----------------------------------------------------------------------|
| Headform      | Pan Head                                                              |
| Drive         | Cross recess Z (Pozidriv)                                             |
| Thread        | fully threaded                                                        |
| Material      | Stainless steel                                                       |
| Material type | A4                                                                    |
| Standard      | DIN 7981 C (Standard withdrawn), ~ISO 7049, ~UNI 6954 AB, ~ČSN 021235 |

| Article no | d1    | L   | d2 max | k max | Pozidriv | m~  |
|------------|-------|-----|--------|-------|----------|-----|
| 3061514    | ST2,2 | 6.5 | 4.2    | 1.8   | 1        | 2.4 |
| 3061515    | ST2,2 | 9.5 | 4.2    | 1.8   | 1        | 2.4 |
| 3061516    | ST2,2 | 13  | 4.2    | 1.8   | 1        | 2.4 |
| 3061517    | ST2,2 | 16  | 4.2    | 1.8   | 1        | 2.4 |
| 3061518    | ST2,2 | 19  | 4.2    | 1.8   | 1        | 2.4 |
| 3061519    | ST2,9 | 6.5 | 5.6    | 2.2   | 1        | 2.9 |
| 3061520    | ST2,9 | 9.5 | 5.6    | 2.2   | 1        | 2.9 |
| 3061522    | ST2,9 | 13  | 5.6    | 2.2   | 1        | 2.9 |
| 3061523    | ST2,9 | 16  | 5.6    | 2.2   | 1        | 2.9 |
| 3061524    | ST2,9 | 19  | 5.6    | 2.2   | 1        | 2.9 |
| 3061526    | ST2,9 | 22  | 5.6    | 2.2   | 1        | 2.9 |
| 3061528    | ST2,9 | 25  | 5.6    | 2.2   | 1        | 2.9 |
| 3061529    | ST3,5 | 6.5 | 6.9    | 2.6   | 2        | 3.9 |
| 3061530    | ST3,5 | 9.5 | 6.9    | 2.6   | 2        | 3.9 |
| 3061532    | ST3,5 | 13  | 6.9    | 2.6   | 2        | 3.9 |
| 3061533    | ST3,5 | 16  | 6.9    | 2.6   | 2        | 3.9 |
| 3061535    | ST3,5 | 19  | 6.9    | 2.6   | 2        | 3.9 |
| 3061536    | ST3,5 | 22  | 6.9    | 2.6   | 2        | 3.9 |

| Article no | d1      | L   | d2 max | k max | Pozidriv | m~  |
|------------|---------|-----|--------|-------|----------|-----|
| 3061537    | ST3,5   | 25  | 6.9    | 2.6   | 2        | 3.9 |
| 3061538    | ST3,5   | 32  | 6.9    | 2.6   | 2        | 3.9 |
| 3061539    | ST3,5   | 38  | 6.9    | 2.6   | 2        | 3.9 |
| 3061540    | (ST3,9) | 6.5 | 7.5    | 2.8   | 2        | 4.1 |
| 3061541    | (ST3,9) | 9.5 | 7.5    | 2.8   | 2        | 4.1 |
| 3061542    | (ST3,9) | 13  | 7.5    | 2.8   | 2        | 4.1 |
| 3061543    | (ST3,9) | 16  | 7.5    | 2.8   | 2        | 4.1 |
| 3061544    | (ST3,9) | 19  | 7.5    | 2.8   | 2        | 4.1 |
| 3061545    | (ST3,9) | 22  | 7.5    | 2.8   | 2        | 4.1 |
| 3061546    | (ST3,9) | 25  | 7.5    | 2.8   | 2        | 4.1 |
| 3061548    | (ST3,9) | 32  | 7.5    | 2.8   | 2        | 4.1 |
| 3061549    | (ST3,9) | 38  | 7.5    | 2.8   | 2        | 4.1 |
| 5805750    | ST4,2   | 6.5 | 8.2    | 3.05  | 2        | 4.3 |
| 3061550    | ST4,2   | 9.5 | 8.2    | 3.05  | 2        | 4.3 |
| 3061552    | ST4,2   | 13  | 8.2    | 3.05  | 2        | 4.3 |
| 3061553    | ST4,2   | 16  | 8.2    | 3.05  | 2        | 4.3 |
| 3061554    | ST4,2   | 19  | 8.2    | 3.05  | 2        | 4.3 |
| 3061555    | ST4,2   | 22  | 8.2    | 3.05  | 2        | 4.3 |
| 3061556    | ST4,2   | 25  | 8.2    | 3.05  | 2        | 4.3 |
| 3061557    | ST4,2   | 32  | 8.2    | 3.05  | 2        | 4.3 |
| 3061558    | ST4,2   | 38  | 8.2    | 3.05  | 2        | 4.3 |
| 3061559    | ST4,2   | 45  | 8.2    | 3.05  | 2        | 4.3 |
| 3061560    | ST4,2   | 50  | 8.2    | 3.05  | 2        | 4.3 |
| 5805760    | ST4,2   | 60  | 8.2    | 3.05  | 2        | 4.3 |
| 5805770    | ST4,8   | 9.5 | 9.5    | 3.55  | 2        | 4.7 |
| 3061561    | ST4,8   | 13  | 9.5    | 3.55  | 2        | 4.7 |
| 3061562    | ST4,8   | 16  | 9.5    | 3.55  | 2        | 4.7 |
| 3061563    | ST4,8   | 19  | 9.5    | 3.55  | 2        | 4.7 |
| 3061564    | ST4,8   | 22  | 9.5    | 3.55  | 2        | 4.7 |
| 3061565    | ST4,8   | 25  | 9.5    | 3.55  | 2        | 4.7 |
| 3061566    | ST4,8   | 32  | 9.5    | 3.55  | 2        | 4.7 |
| 3061568    | ST4,8   | 38  | 9.5    | 3.55  | 2        | 4.7 |
| 3061569    | ST4,8   | 45  | 9.5    | 3.55  | 2        | 4.7 |
| 3061570    | ST4,8   | 50  | 9.5    | 3.55  | 2        | 4.7 |
| 3061571    | ST4,8   | 60  | 9.5    | 3.55  | 2        | 4.7 |
| 3061574    | ST4,8   | 70  | 9.5    | 3.55  | 2        | 4.7 |
| 3061575    | ST4,8   | 80  | 9.5    | 3.55  | 2        | 4.7 |
| 3061785    | ST5,5   | 13  | 10.8   | 3.95  | 3        | 6.2 |
| 3061789    | ST5,5   | 16  | 10.8   | 3.95  | 3        | 6.2 |
| 3061790    | ST5,5   | 19  | 10.8   | 3.95  | 3        | 6.2 |
| 3061791    | ST5,5   | 22  | 10.8   | 3.95  | 3        | 6.2 |
| 3061792    | ST5,5   | 25  | 10.8   | 3.95  | 3        | 6.2 |
| 3061793    | ST5,5   | 32  | 10.8   | 3.95  | 3        | 6.2 |
| 3061794    | ST5,5   | 38  | 10.8   | 3.95  | 3        | 6.2 |
| 3061795    | ST5,5   | 45  | 10.8   | 3.95  | 3        | 6.2 |
| 3061796    | ST5,5   | 50  | 10.8   | 3.95  | 3        | 6.2 |
| 3061797    | ST5,5   | 60  | 10.8   | 3.95  | 3        | 6.2 |
| 3061798    | ST5,5   | 70  | 10.8   | 3.95  | 3        | 6.2 |
| 3061799    | ST5,5   | 80  | 10.8   | 3.95  | 3        | 6.2 |
| 3061800    | ST6,3   | 13  | 12.5   | 4.55  | 3        | 6.7 |

| Article no | d1    | L  | d2 max | k max | Pozidriv | m~  |
|------------|-------|----|--------|-------|----------|-----|
| 3061801    | ST6,3 | 16 | 12.5   | 4.55  | 3        | 6.7 |
| 3061802    | ST6,3 | 19 | 12.5   | 4.55  | 3        | 6.7 |
| 3061803    | ST6,3 | 22 | 12.5   | 4.55  | 3        | 6.7 |
| 3061804    | ST6,3 | 25 | 12.5   | 4.55  | 3        | 6.7 |
| 3061805    | ST6,3 | 32 | 12.5   | 4.55  | 3        | 6.7 |
| 3061806    | ST6,3 | 38 | 12.5   | 4.55  | 3        | 6.7 |
| 3061807    | ST6,3 | 45 | 12.5   | 4.55  | 3        | 6.7 |
| 3061808    | ST6,3 | 50 | 12.5   | 4.55  | 3        | 6.7 |
| 3061809    | ST6,3 | 60 | 12.5   | 4.55  | 3        | 6.7 |
| 3061810    | ST6,3 | 70 | 12.5   | 4.55  | 3        | 6.7 |
| 3061811    | ST6,3 | 80 | 12.5   | 4.55  | 3        | 6.7 |