


REINFORCED



FEATURES

- ✓ Reinforced with microswitch, strength up to 1000 kgs.
- ✓ Reversible (left and right hand).
- ✓ Symmetrical.
- ✓ Height 85 mm., width 21,5 mm.
- ✓ Fail - secure (NC) and fail-safe (NO) models.
- ✓ Assembling screws distance 52 mm.
- ✓ Power supply: 6, 12, 24, 48 V AC / DC.
- ✓ Micro switch load: 3A-12V AC; 2A-30V DC.
- ✓ 24 hours working models.
- ✓ Low or very low power consumption.
- ✓ Working temperature for NO electric strikes is 60°C.

TECHNICAL DATA



Model		
Standard	Low consump.	NO
1560	1568	1561

Power supply (V)	6-12V AC/DC Standard	12-24V AC/DC Standard	12-24V AC/DC Low consump. 12V	24-48V AC/DC Low consump. 24V	12V DC NO	24V DC NO
Tolerance (%)	± 5 %					
Continuous work	< 1 min.	< 1 min.	100 % 12V DC <1 min. 12V AC <1 min. 24V AC/DC	100 % 24V DC <1 min. 24V AC <1 min. 48V AC/DC	100 %	100 %
Resistance (Ω)	8,5	20	40	150	60	150
Power consumption DC (mA)	6V / 700 12V / 1400	12V / 600 24V / 1100	12V / 300 24V / 600	24V / 170 48V / 340	12V / 300 -	24V / 170 -
Power consumption AC (mA)	6V / 600 12V / 1200	12V / 500 24V / 1000	12V / 250 24V / 510	24V / 150 48V / 300	-	-
Max preload DC (N)	10	10	10	10	10	10
Max preload AC (N)	90	90	90	90	-	-

Recommended front plates: 900; 901; 902; 904; 903; 913