

Bits for TORX PLUS® Screws



EAN:	4013288106568	Size:	50x7x6 mm
Part number:	05134668001	Weight:	8 g
Article number:	867/4 IP TORX PLUS®	Country of origin:	CZ
		Customs tariff number:	82079030

- For TORX PLUS® screws
- Ductile and tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)
- Suitable for AEG, ARÖ, Atlas-Copco, Biax, Black & Decker, Bosch, Buckeye Tools etc.
- Prevents premature breakage of the drive tip

High quality bits for recessed TORX PLUS® screws. TORX PLUS® profile: in comparison to normal TORX® profiles, the enlargement of the 6 torque-transferring flanks between the tool and the screw is effected by means of an ellipse-shaped profile design and not a circular one. This means that the power applied when screwdriving is spread over a larger area. Higher torque is transferred and the service life of the screw and tool is also enhanced. Tough viscous for universal use. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_torx_plus_screws_867_4_ip_torx_plus.html

Wera - 867/4 IP TORX PLUS®
05134668001 - 4013288106568

Wera Werkzeuge GmbH
Körzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for TORX PLUS® Screws

TORX PLUS®



Compared with the "normal" TORX® profile, the elliptical instead of circular profile enlarges the 6 flanks that transfer torque between the tool and the screw. This means that the force applied when screwdriving is spread across a larger surface area. Higher torque is transferred and, in addition, the service life of the screw and tool are lengthened. The so-called centre-lock screws on cutting tools represent a typical use of this type of screw profile. The thermal influences on such holders for carbide insert tips often "bake" the retaining screws so firmly that it is important to have a profile that considerably enhances the loosening torque capability of the screws. For this reason a torque-stable screw profile is necessary to avoid any possible damage to the screw and to exclude the possibility of an otherwise costly machine downtime.

Tough-absorbing bits



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_torx_plus_screws_867_4_ip_torx_plus.html

Wera - 867/4 IP TORX PLUS®
05134668001 - 4013288106568

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Bits for TORX PLUS® Screws

Further versions in this product family:

		 mm	 inch	 mm
05134664001	1 IP	50	2	2.0
05134665001	2 IP	50	2	2.0
05134668001	3 IP	50	2	2.0
05134691001	4 IP	50	2	3.0
05134678001	5 IP	50	2	3.0
05134680001	6 IP	50	2	3.0
05134667001	6 IP	89	3 1/2	3.0
05134690001	6 IP	152	6	3.0
05134681001	7 IP	50	2	3.0
05134679001	8 IP	50	2	3.0
05134670001	8 IP	89	3 1/2	3.0
05134682001	8 IP	152	6	3.0
05160917001	9 IP	50	2	3.0
05134669001	9 IP	89	3 1/2	3.0
05134683001	10 IP	50	2	4.0
05134684001	10 IP	70	2 3/4	4.0
05134671001	10 IP	89	3 1/2	4.0
05134685001	15 IP	50	2	4.0
05134686001	15 IP	70	2 3/4	4.0
05134672001	15 IP	89	3 1/2	4.0
05134687001	20 IP	50	2	4.5
05134688001	20 IP	70	2 3/4	4.5
05134673001	20 IP	89	3 1/2	4.5
05134609001	25 IP	50	2	6.0
05134674001	25 IP	89	3 1/2	6.0
05134675001	27 IP	89	3 1/2	6.0
05320430001	30 IP	50	2	6.0
05134676001	30 IP	89	3 1/2	6.0
05134677001	40 IP	89	3 1/2	-

Web link

https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_torx_plus_screws_867_4_ip_torx_plus.html

Wera - 867/4 IP TORX PLUS®
 05134668001 - 4013288106568

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de