

SPECIFICATIONS

[General Specifications]


Model	5 tiers	MP-502
	4 tiers	MP-402
	3 tiers	MP-302
	2 tiers	MP-202
	1 tier	MP-102
UL Registered Model		MP-_02
Rated Voltage		24V AC/DC (50/60Hz)
Operating Voltage Range		Rated Voltage ±10%
Signal Wire Current	Typ.	Per Unit
		Red:29.0mA, Amber:29.5mA, Green:17.1mA, Blue:17.1mA, White:17.1mA
	Max.	Per Unit
		Red:32.7mA, Amber:34.5mA, Green:21.4mA, Blue:21.4mA, White:21.4mA
Operating Ambient Temperature		-30°C to +60°C
Operating Ambient Humidity		Less than 90% (No condensation)
Mounting Location		Indoors
Mounting Direction		Upright
Protection Rating		IP65 (IEC 60529)
Vibration Resistance		19.6m/s²
Insulation Resistance		More than 1MΩ at 500VDC between the terminals and the chassis
Withstand Voltage		500VAC applied for 1min between terminals and chassis without breaking insulation
Luminous Intensity		Red:550mcd, Amber:650mcd, Green:1900mcd, Blue:700mcd, White:1600mcd
Mass (Tolerance ±10%)		1 tier:0.21kg, 2 tiers:0.23kg, 3 tiers:0.25kg, 4 tiers:0.27kg, 5 tiers:0.29kg
Outer Dimensions		Refer to the Outer Dimension Drawing
Conformity Standards		EMC Directive (EN 61000-6-4, EN 61000-6-2) RoHS Directive (EN IEC 63000) UL 508, CSA-C22.2 No. 14
Remarks		Conforms to the CE requirements UL Recognized Component (File No.E215660)

Model Number Configuration

MP — 02 —


Tier	Luminous Color
1 : 1 tier	R : Red
2 : 2 tiers	Y : Amber
3 : 3 tiers	G : Green
4 : 4 tiers	B : Blue
5 : 5 tiers	C : White

PATLITE Corporation




指定公差 General tolerance		角度公差 Angular tolerance ±[°]		寸法公差 Dimensional tolerance ±[mm]		図番 Drawing No.		ページ Page	
短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	MP-502-W18		2 / 2	
	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	改訂 Rev.	年月日 Date	改訂履歴 Revisions	
	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side				
	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side	短辺長さ Length of short side				

Wiring Example (wire:UL1007/AWG22)



Transistor drive example(24V DC)



Note

- When wiring is completed, insulate the end of each unused wire with insulation tape.
- Use a "Class 2 Circuit" for power supply source.
- Use the fusefolder authorized by UL standard.
- Use the fuse conforming to the rated current of the machine which the product was installed on.
(Example : Class J type fuse)
- Fasten nut with the torque of 3.5±0.5N·m.

6	Waterproof Sheet	1	CR, Black
5	O Ring	n+1	Si, Gray
4	Nut	1	M22, P=1.5
3	Body	1	ABS, Silver coating
2	LED Unit	n	Lens:AS/Reflector:ABS
1	Head Cover	1	ABS, Silver coating
番号 No.	部品名 Part Name	数量 Qty.	記事 Remarks
機種 Model	MP-502	特注No. S.P.No.	図名 Name
品目コード Part No.	-	尺度 Scale	三角法 3rd Angle P.
		1:2	単位 Unit
			mm
			株式会社 PATLITE Corporation