

Type TXF Subminiature Time Delay Fuse - 3.6 x 10mm



www.optifuse.com

(619) 593-5050

Time Characteristics:

100%	4h Min.	200mA-10A
200%	60s Max. 1-60s	200mA-800mA 1A-10A


Interrupt Rating:

200mA~ 1.6A 30A at 350 VAC
2A ~ 10A 50A at 350 VAC


Packaging:

1,500 pieces taped and ammo pack

Time Current Curve Graph



Mechanical Dimensions:



Epoxy Coated

Part Number	Amperage	Rated Voltage (VAC)	I ² T Reference A ² Sec
TXF-200mA	200mA	350V	0.0200
TXF-250mA	250mA		0.0352
TXF-300mA	300mA		0.0562
TXF-315mA	315mA		0.0620
TXF-350mA	350mA		0.0765
TXF-375mA	375mA		0.0878
TXF-400mA	400mA		0.107
TXF-500mA	500mA		0.219
TXF-600mA	600mA		0.387
TXF-630mA	630mA		0.427
TXF-700mA	700mA		0.642
TXF-750mA	750mA		0.742
TXF-800mA	800mA		1.000
TXF-1A	1A		2.692
TXF-1.2A	1.2A		3.825
TXF-1.25A	1.25A		4.111
TXF-1.5A	1.5A		6.252
TXF-1.6A	1.6A		7.113
TXF-2A	2A		13.14
TXF-2.25A	2.25A		17.46
TXF-2.5A	2.5A		20.32
TXF-3A	3A		31.05
TXF-3.15A	3.15A		34.23
TXF-3.5A	3.5A		44.25
TXF-4A	4A		58.34
TXF-5A	5A		90.36
TXF-6A	6A		86.25
TXF-6.3A	6.3A		95.09
TXF-7A	7A		120.8
TXF-8A	8A		175.4
TXF-9A	9A		228.6
TXF-10A	10A		297.8

Warning:



-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of Fuse device with chemical solvent. Prolonged contact may damage the device performance.