


■Features

- High Luminous LEDs
- 3mm Flat Top Standard Directivity
- UV Resistant Epoxy
- White Diffused
- Bi-polar Type

■Applications

- Toys
- Games
- Audio
- General Purpose

■Outline Dimension




■Absolute Maximum Rating

($T_a=25^\circ\text{C}$)

Item	Symbol	Value		Unit
		YL	YG	
DC Forward Current	I_F	30	30	mA
Pulse Forward Current#	I_{FP}	100	100	mA
Reverse Voltage	V_R	5	5	V
Power Dissipation	P_D	78	78	mW
Operating Temperature	T_{opr}	$-30 \sim +85$		$^\circ\text{C}$
Storage Temperature	T_{stg}	$-40 \sim +100$		$^\circ\text{C}$
Lead Soldering Temperature	T_{sol}	$260^\circ\text{C}/5\text{sec}$		-

#Pulse width Max.10ms Duty ratio max 1/10

■Directivity



■Electrical -Optical Characteristics

($T_a=25^\circ\text{C}$)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
DC Forward Voltage*1	V_F (YL)	$I_F=20\text{mA}$	1.8	2.1	2.6	V
	V_F (YG)	$I_F=20\text{mA}$	1.8	2.1	2.6	V
DC Reverse Current	I_R	$V_R=5\text{V}$	-	-	10	μA
Domi. Wavelength*2	λ_D (YL)	$I_F=20\text{mA}$	620	625	630	nm
	λ_D (YG)	$I_F=20\text{mA}$	565	570	575	nm
Luminous Intensity*3	I_v (YL)	$I_F=20\text{mA}$	68	100	-	mcd
	I_v (YG)	$I_F=20\text{mA}$	30	45	-	mcd
50% Power Angle	$2\theta_{1/2}$	$I_F=20\text{mA}$	-	140	-	deg

*1 Tolerance of measurements of forward voltage is $\pm 0.1\text{V}$

*2 Tolerance of measurements of peak wavelength is $\pm 1\text{nm}$

*3 Tolerance of measurements of luminous intensity is $\pm 15\%$