

HG 2520 E

Case

EAN 4007841 351601

Article number 351601



CE



VDE

Function description

The reference in pistol form. Electronically controlled hot air tool HG 2520 E with brushless motor, digital temperature adjustment by joystick from 50 – 700 °C. Airflow control from 150 – 500 l/min. Includes LCD display and residual heat indicator. Suitable for use on construction sites.

Technical specifications

Output	2300 W
Temperature	50 – 700 °C
Airflow rate	150 – 500 l/min
Air pressure	4000 Pa
Motor, type	Brushless
Function, life expectancy, motor	10000 h
Temperature setting	in 10°C steps by joystick
Temperature display	LCD display
Heating element	Ceramic heating element
Loc function	Yes
Residual heat indicator	Yes

Function, hanger	Yes
Replaceable heating element	Yes
Restart protection	No
Thermal cut-out	Yes
Thermostat	Yes
Cord length	3 m
Dimensions (L x W x H)	286 x 96 x 207 mm
Mains power supply	220 – 230 V / 50 – 60 Hz
PU1, net weight	1,283 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841351601

HG 2520 E

Case

EAN 4007841 351601

Article number 351601

**Accessories**

EAN 4007841 007690	HG Scan for HG 2520 E
EAN 4007841 064822	Hot Air Tool Guard Cage HG 2520 E
EAN 4007841 093211	Pressure roller 50mm - Rubber
EAN 4007841 009106	Fast welding nozzle 3mm narrow - for 5mm rd. noz.
EAN 4007841 009090	Flat nozzle 60x2 mm for bitumen
EAN 4007841 011925	Flat angled nozzle 30x2 mm, 60°
EAN 4007841 010423	Tarpaulin shears
EAN 4007841 093013	Stamped steel plate weld slide
EAN 4007841 011833	Fillet weld feeder
EAN 4007841 011765	Fast welding nozzle 4mm narrow - for 5mm rd. noz.
EAN 4007841 010263	Fast welding nozzle 3mm - for 5mm rd. noz.
EAN 4007841 010270	Fast welding nozzle 4mm - for 5mm rd. noz.
EAN 4007841 073114	PVC plastic welding rod
EAN 4007841 071219	HDPE plastic welding rod
EAN 4007841 034566	HL Tool Stand
EAN 4007841 011840	Fast welding nozzle 5mm narrow - for 5mm rd. noz.
EAN 4007841 092016	Flat angled nozzle 40x2 mm
EAN 4007841 009076	Round nozzle extended 5 mm
EAN 4007841 010287	Fast welding nozzle 5mm - for 5mm rd. noz.
EAN 4007841 013240	Flat angled nozzle 20x2 mm - straight
EAN 4007841 011888	Shell reflector nozzle 150 x 25 mm
EAN 4007841 010409	Sieve reflector nozzle 50 x 35 mm
EAN 4007841 092917	Quarter-moon crucible steel knife
EAN 4007841 075316	Fast welding nozzle 5mm narrow - for 10mm rd. noz.
EAN 4007841 011857	Reflector nozzle 20mm
EAN 4007841 006785	Pressure roller 40mm - Silicone
EAN 4007841 092313	Round nozzle 10 mm
EAN 4007841 009083	Flat nozzle 40x2 mm perforated
EAN 4007841 074210	ABS plastic welding rod
EAN 4007841 011871	Soldering reflector nozzle
EAN 4007841 092115	Flat angled nozzle 20x2 mm - angled
EAN 4007841 007812	Flat angled nozzle 20x2 mm, 100°
EAN 4007841 011864	Reflector nozzle 35mm
EAN 4007841 093112	Jointing plane including replacement blade
EAN 4007841 034122	Pressure roller 40mm - Teflon
EAN 4007841 0104166	Sieve reflector nozzle 35 x 20 mm
EAN 4007841 073411	PP plastic welding rod
EAN 4007841 009212	Heating element HG 2620 E / HG 2520 E