


■Features

- High Luminous Output
- 2.5*5.0*8.7mm Rectangular
- White Diffused Type
- Common Anode Type

■Applications

- TV Set
- Telephone
- Audio
- Circuit Board

■Outline Dimension




■Absolute Maximum Rating (Ta=25°C)

Item	Symbol	Value		Unit
		Red	Green/Blue	
DC Forward Current	I_F	30	30	mA
Pulse Forward Current#	I_{FP}	100	100	mA
Reverse Voltage	V_R	5	5	V
Power Dissipation	P_D	72	102	mW
Operating Temperature	T_{opr}	$-30 \sim +85$		°C
Storage Temperature	T_{stg}	$-40 \sim +100$		°C
Lead Soldering Temperature	T_{sol}	260°C/5sec		—

#Pulse width Max.10ms Duty ratio max 1/10

■Directivity



■Electrical -Optical Characteristics (Ta=25°C)

Item	Symbol	Condition	Min.	Typ.	Max.	Unit
DC Forward Voltage*1	$V_F(\text{R})$	$I_F=20\text{mA}$	-	2.1	2.4	V
	$V_F(\text{B/G})$	$I_F=20\text{mA}$	-	2.9	3.4	V
DC Reverse Current	I_R	$V_R=5\text{V}$	-	-	10	μA
Domi. Wavelength*2	$\lambda_D(\text{Red})$	$I_F=20\text{mA}$	620	625	630	nm
	$\lambda_D(\text{Green})$	$I_F=20\text{mA}$	520	525	530	nm
	$\lambda_D(\text{Blue})$	$I_F=20\text{mA}$	465	470	475	nm
Luminous Intensity*3	$I_v(\text{Red})$	$I_F=20\text{mA}$	330	500	-	mcd
	$I_v(\text{Green})$	$I_F=20\text{mA}$	500	750	-	mcd
	$I_v(\text{Blue})$	$I_F=20\text{mA}$	220	330	-	mcd
50% Power Angle	$2\theta_{1/2}$	$I_F=20\text{mA}$	-	100	-	deg

*1 Tolerance of measurements of forward voltage is $\pm 0.1\text{V}$

*2 Tolerance of measurements of dominant wavelength is $\pm 1\text{nm}$

*3 Tolerance of measurements of luminous intensity is $\pm 15\%$