

5957VI

Assortment of 162 tools

Industrial maintenance

		art.
	059571005	5957VI



- n. 6 **31/SP6:** pin punches Ø 2 - 3 - 4 - 5 - 6 - 8 mm
- n. 6 **38/SP6:** 2 drift punches, 1 centre punch, 3 flat chisels with metal holder
- n. 18 **42:** combination wrenches 6-7-8-10-11-12-13-14-15-16-17-19-21-22-24-27-30-32 mm
- n. 12 **55/S12X:** double open end wrenches 6x7 ÷ 30x32 mm
- n. 8 **96T/S8:** offset hexagon key wrenches 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm
- n. 8 **97TX/SC8:** offset key wrenches, for Torx® head screws ⌘ T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
- n. 1 **111E:** 250 mm
- n. 13 **920B/SB13:** 1/2" square drive bi-hex sockets with rail ○ 10÷22 mm
- n. 8 **920B/SB8:** 1/2" square drive bi-hex sockets with rail ○ 23÷32 mm
- n. 4 **920LP:** 1/2" socket drivers for slotted head screws ● 1,2x6,5 - 1,2x8 - 1,6x9 - 2x12 mm
- n. 3 **920PH:** 1/2" socket drivers for Phillips® screws ⊕ PH2 - 3 - 4
- n. 1 **920/21:** 1/2" drive extension bar 125 mm
- n. 1 **920/22:** 1/2" drive extension bar 255 mm
- n. 1 **920/25:** 1/2" drive universal joint
- n. 1 **920/42:** 1/2" drive sliding T-handle
- n. 1 **920/55:** 1/2" drive reversible ratchet ⌚
- n. 1 **963:** pry bar
- n. 2 **1032:** circlip pliers straight, internal ⊙ 140 - 180 mm
- n. 2 **1034:** circlip pliers bent, internal ⊙ 130 - 170 mm
- n. 2 **1036:** circlip pliers straight, external ● 140 - 175 mm
- n. 2 **1038:** circlip pliers bent, external ● 135 - 175 mm
- n. 1 **1048N:** 250 mm
- n. 1 **1051:** self locking pliers, double adjustment
- n. 1 **1084BM:** Heavy-duty diagonal cutting nippers □ 160 mm
- n. 1 **1092V:** toggle lever assisted end cutting nippers □ 180 mm
- n. 1 **1112:** tin snips 250 mm
- n. 1 **1114:** tin snip, straight narrow blades 250 mm
- n. 1 **1128BMX:** electrician's scissors, straight blades
- n. 1 **1150BM:** half-round needle nose pliers = 180 mm
- n. 1 **1166BM:** Extra-long needle nose pliers ● 160 mm
- n. 1 **1168BM:** Extra-long bent needle nose pliers ● 160 mm
- n. 7 **1260:** screwdrivers for slotted head screws ● 2,5x50 - 3x75 - 4x100 5,5x125 - 6,5x150 - 8x200 - 10x200 mm
- n. 4 **1262:** screwdrivers for cross head Phillips® screws ⊕ PH0x60 - PH1x80 - PH2x100 - PH3x150 mm
- n. 3 **1370:** engineer's hammer 300 - 600 - 1000 g
- n. 1 **1390:** soft face hammer Ø 35 mm
- n. 1 **1692:** measuring tape 5 m
- n. 1 **1712E/2:** flexible magnetic pick-up tool 1,8 kg
- n. 1 **1717A:** two cutting edges scraper 200 mm
- n. 1 **1717B:** three - cutting edges scraper 200 mm