


C4AU0BU4500M11J

C4AU, Film, Metallized Polypropylene, Automotive DC Link, 5 uF, 5%, 900 VDC, Lead Spacing = 27.5mm



Click [here](#) for the 3D model.

Dimensions

L	32mm +/-0.7mm
H	29mm +/-0.7mm
T	19mm +/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	72

General Information

Series	C4AU
Dielectric	Metallized Polypropylene
Style	Radial
Features	DC Filtering
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Component Weight	26.7 g
Miscellaneous	Rth = 29 C/W.

Specifications

Capacitance	5 uF
Capacitance Tolerance	5%
Voltage DC	900 VDC
Temperature Range	-55/+105°C
Insulation Resistance	6 GOhms
Max dV/dt	70 V/us
Resistance	8.8 mOhms (10kHz 70C)
Ripple Current	10.2 Amps Irms (10kHz 95C), 350 Amps Ipk
Inductance	25 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.