


C4AQIBU4800M11J

C4AQ-M, Film, Metallized Polypropylene, Automotive DC Link, 8 uF, 5%, 800 VDC, 85°C, Lead Spacing = 27.5mm



Click [here](#) for the 3D model.

Dimensions

L	31.5mm +0.5/-0.7mm
H	29mm +0.2/-0.7mm
T	19mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	72

General Information

Series	C4AQ-M
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Component Weight	25.8 g
Miscellaneous	Rth = 29 C/W.

Specifications

Capacitance	8 uF
Capacitance Tolerance	5%
Voltage DC	800 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Insulation Resistance	3.8 GOhms
Max dV/dt	65 V/us
Resistance	7.3 mOhms (10kHz 70C)
Ripple Current	11.2 Amps Irms (10kHz 70C), 520 Amps Ipk
Inductance	25 nH